

F81 Drop Connectors - Precision F81 Connector 3 GHz "F" Female Splice



For more Information
please call

1-800-Belden1



General Description:

Precision F81 Connector 3 GHz "F" Female Splice, Splice

Usage (Overall)

Suitable Applications: Broadband, CATV

Physical Characteristics (Connectivity)

Product Family:

Part Number	Cable O.D. (mm)	Description	Inner Pack	Outer Pack
TBCF81	1.067	Precision F81 Connector 3 GHz F Female Splice	100	2000

Connector Type: Precision Splice

Body: Zinc

Body Finish: Nickel

Mechanical Characteristics (Connectivity)

Cable Retention Force: 200 grams

Temperature Rating: -40°C To +70°C

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

EU Directive 2002/95/EC (RoHS): Yes

EU RoHS Compliance Date (mm/dd/yyyy): 11/27/2008

Electrical Characteristics (Overall)

Frequency Range: 5 MHz TO 3 GHz

Nominal Impedance: 75 Ohms

Return Loss (typical): >= -24 dB up to 3 GHz, >=-30 dB up to 1 GHz

Insertion Loss: <=-0.20 dB up to 1 GHz, <= -0.25 dB up to 3 GHz

Shielding Effectiveness (Min.): 100 dB

Band Flatness (min.): 0.1 dB @ 3 GHz

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
--------	-------	-------------	-------	-------	-----------

Revision Number: 0 Revision Date: 08-26-2011

© 2016 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS (Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be in stock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.