## NSYCVF550M230FB

ClimaSys CVHD outdoor HD fan-box without grille and filter 550 m3/h 230VAC



Main		
Range	ClimaSys	
Product name	ClimaSys CV	
Product or component-type	Fanbox without grille and filter	
Product specific application	Outdoor heavy duty	
Range compatibility	Spacial SFHD Spacial S3HD Thalassa PHD	
Air flow	550 m3/h at 60 Hz Free flow rate: 550 m3/h at 50 Hz	
[Us] rated supply voltage	230 V AC +/- 10 %	
Input voltage	230 V AC 50/60 Hz	
Product certifications	Ecodesign directive 2009/125/EC UL conforming to UL 508 A CSA conforming to CSA C22.2 CE	

Complementary

o in promonary		
Power range	7288 W	
[In] rated current	0.30.4 A 50 Hz	
Noise level	60 dB	
Bearing type	Ball	
Height	External: 223 mm	
Width	External: 223 mm	
Depth	External: 90 mm	
Product weight	1.7 kg	
Colour	Dark grey RAL 7016	
Ambient air temperature for operation	-4065 °C	
Ambient air temperature for storage	-4080 °C	
Maximum pressure	350 Pa flow rate 0 m³/h	
Connections - terminals	Spring clamp terminal	
IP degree of protection	IP55 with grid (NSYCAG223LFHD) IP44	
Device composition	1 fanbox 4 screw	
Condition of use	Outside temperature must be 5 °C lower than inside temperature Filter must be cleaned and replaced regularly Surrounding environment must be relatively clean Overfrequent filter replacement should be avoided Flow rates depends on the work point, see ProClima software	

## Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0940 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold

Product Life Status:	Commercialised
Product Life Status:	Commercialise