


Category 8 24 Port Patch Panel



Category 8 24 Port Patch Panel (SEF24mc)

This Category 8 panel offers outstanding performance with exceptional value for money.

Features

- Transmission performance in compliance with the ANSI/TIA 568-C.2-1 specifications for Category 8 cabling systems (i. e. suitable for runs of 5 – 30 metres)
- Compliant with IEC60512-99-001 – suitable for use with IEEE 802.3at (PoE+) applications
- Connectors provide quick and easy tool-less lever “butterfly style” termination
- Suitable for 0.51 – 0.65 mm/ 22 – 24 AWG stranded and solid wire
- Mounts to any standard 19-inch rack, cabinet or wall bracket
- Clear numbering on the front provides a quick, easy way to identify cable run
- ‘Slip-in’ label facility for port identification
- High quality removable metal rear cable management with earthing

Specifications

- Weight: 1450g (approx.)
- Dimensions: 482 x 44 x 107mm (approx.)
- Colour: black

- Materials:
 - Category 8 keystone:
 - Body: nickel-plated die-cast zinc
 - RJ45 contacts: 50μ"/1.27μm gold-plated phosphor bronze
 - IDC contacts: tin-plated phosphor bronze
 - Tape: copper foil
 - Panel:
 - Frame:
 - Front: Black coated cold rolled steel
 - Back: Zinc coated cold rolled steel
 - Cable management bar: Black coated cold rolled steel

Packaging: Supplied as a kit in individual carton

EAN number: 5055386506603

Commodity Code: 85177090

