Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



73409W Multi-Conductor - 600V Unshielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles



For more Information please call

1-800-Belden1

General Description:

14 AWG stranded (41x30) bare copper conductors, PVC insulation, oil-resistant PVC jacket.

Physical Characteristics (Overall) Conductor AWG: # Conductors AWG Stranding Conductor Material 14 41x30 BC - Bare Copper **Total Number of Conductors:** 9 **Ground Wire** Ground Wire (Y/N): Ground Wire AWG: 14 **Ground Wire Stranding:** 41x30 **Ground Wire Conductor Material:** BC - Bare Copper **Ground Wire Insulation Material:** PVC - Polyvinyl Chloride

Insulation

Insulation Material:

| Insulation Material | Wall Thickness (in.) | PVC - Polyvinyl Chloride | 0.022

Insulation Color Code Chart:

Color Description

Black Individually Numbered

Outer Shield

Outer Shield Material:

Outer Shield Material Unshielded

Outer Jacket

Outer Jacket Material:

Outer Jacket Material Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride | 0.063

Overall Cable

Overall Nominal Diameter: 0.609 in.

Mechanical Characteristics (Overall)					
Storage Temperature Range:		-40°C To +90°C			
Installation Temperature Ran	ge:	Flexing: -5°C To +90°C			
Bulk Cable Weight:		500 lbs/1000 ft.			
Max. Recommended Pulling	ension:	290 lbs.			
Min. Bend Radius/Minor Axis	:	3 in.			
Min. Bend/Installation:		3 in.			
Min. Bend Radius (Continuou	s Flexing):	3 in.			
Flex Cycle Rating:		1 Million Flexes			

Applicable Specifications and Agency Compliance (Overall)

Applicable Standards & Environmental Programs

AWM Specification:	UL Style 2587 (600 V 90°C)		
CSA Specification:	600 V AWM I/II A/B		
EU Directive 2011/65/EU (ROHS II):	Yes		
MII Order #39 (China RoHS):	Yes		
Other Specification:	VDE 0472, Section 803 Oil Test, EU Low Voltage Directive 2014/35/EC, EU Directive 2011/65/EU(RoHS2), REACH Regulation (EC 1907/2006), California Proposition 65		

Flame Test

Page 1 of 2 10-02-2017

Detailed Specifications & Technical Data

ENGLISH MEASUREMENT VERSION



73409W Multi-Conductor - 600V Unshielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles

•	CSA Flame Test:	FI1				
Suita	Suitability					
:	Suitability - Burial:	Yes				
Elect	trical Characteristics (Overall)					
Nom.	Inductance:					
	ductance (μH/ft) 170					
Max.	Max. Capacitance Conductor to Conductor:					
Fr	req. (MHz) Capacitance (pF/ft)					
0.0	001 36.000					
Nom.	Conductor DC Resistance:					
DO	CR @ 20°C (Ohm/1000 ft)					
2.0	600					
Max.	Operating Voltage - UL:					
	oltage 00V					

Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
73409W 008100	100 FT	57.100 LB	GRAY		14AWG 41/30 9C UNSHIELDED
73409W 008500	500 FT	290.000 LB	GRAY		14AWG 41/30 9C UNSHIELDED

Revision Date: 09-27-2017 Revision Number: 0

© 2017 Belden, Inc All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Page 2 of 2