

## Label, highly flexible - MM-EMLF (EX10)R C1 RD/WH - 0803959

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Highly flexible label, continuous, cassette, red with white imprint, mounting type: adhesive, can be marked with THERMOFOX

### Key Commercial Data

|                                      |               |
|--------------------------------------|---------------|
| Packing unit                         | 1 STK         |
| GTIN                                 |               |
| GTIN                                 | 4055626212364 |
| Weight per Piece (excluding packing) | 58.100 g      |
| Custom tariff number                 | 39199080      |
| Country of origin                    | China         |

### Technical data

#### Dimensions

|            |         |
|------------|---------|
| Length (b) | 8000 mm |
| Width (a)  | 10 mm   |

#### Ambient conditions

|                                 |   |
|---------------------------------|---|
| Ambient temperature (operation) | -20 °C ... 75 °C  |
| Recommended storage conditions  | 20°C/50% relative humidity. Storage in the original packaging is recommended. |

#### General

|                 |                                |
|-----------------|--------------------------------|
| Color           | red                            |
| Components      | Free from silicone and cadmium |
| Material        | Vinyl polymer                  |
| RoHS compliant  | Yes                            |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1)    |
| Adhesive        | Acrylic                        |
| Printability    | Thermal transfer               |

# Label, highly flexible - MM-EMLF (EX10)R C1 RD/WH - 0803959

## Technical data

### General

|   |                                     |
|---|-------------------------------------|
| Device  | 0803984 THERMOFOX                   |
| Test for substances that would hinder coating with paint or varnish | VW PV 3.10.7:2005-02                |
| Result  | Test passed                         |
| Test specification weathering-resistance                            | Following ISO 4892-2:2013-03        |
| Test duration   | 96 h                                |
| Wipe resistance test result   | Test passed                         |
| Salt spray test specification                                       | DIN EN 60068-2-11:2000-02           |
| Test duration   | 96 h                                |
| Salt spray testing result   | Test passed                         |
| Wipe resistance of test specification inscriptions                  | DIN EN 61010-1 (VDE 0411-1):2011-07 |
| Result  | Test passed                         |
| Marking mounting type   | adhesive                            |

### Standards and Regulations

|                 |                             |
|-----------------|-----------------------------|
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
|-----------------|-----------------------------|

### Environmental Product Compliance

|            |   |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
|            | No hazardous substances above threshold values          |

## Classifications

### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190219 |
| eCl@ss 4.1 | 24190219 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |
| eCl@ss 8.0 | 27149129 |
| eCl@ss 9.0 | 27400629 |

### ETIM

|          |          |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC001288 |
| ETIM 6.0 | EC001288 |

### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |

## Label, highly flexible - MM-EMLF (EX10)R C1 RD/WH - 0803959

### Classifications

#### UNSPSC

|              |          |
|--------------|----------|
| UNSPSC 11    | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2  | 39131504 |