



TUBULAR HEATERS AND GUARDS

- TUBULAR HEATER**
- Steel construction
 - Thermal overload cut out
 - Pre-wired with 1m mains lead: easy installation
 - Additional locking cable gland included for through wiring / linking to other tubular heaters
 - Mounting brackets included for wall or floor installation
 - Low wattage solution for localised background heat and frost protection

- TUBULAR HEATER GUARD**
- Steel construction
 - Robustly constructed wire guard: provides protection and safety
 - Colour matches tubular heater
 - Aesthetically pleasing curved design
 - Fixing kit included

- **TH1** = M.O.M: 1 / O.P.Q: 20
- **TH2** = M.O.M: 1 / O.P.Q: 12
- **TH3** = M.O.M: 1 / O.P.Q: 9
- **TH4** = M.O.M: 1 / O.P.Q: 6
- **TRG1FT** = M.O.M: 2 / O.P.Q: 18
- **TRG2FT** = M.O.M: 2 / O.P.Q: 12
- **TRG3FT** = M.O.M: 2 / O.P.Q: 6
- **TRG4FT** = M.O.M: 2 / O.P.Q: 6



Mounting brackets & additional locking cable gland included

4 Sizes Available



1FT

2FT


3FT

4FT




Mains supply cap

Spare cable clamp




- TH1:** 305mm
- TH2:** 600mm
- TH3:** 915mm
- TH4:** 1220mm



- TRG1FT:** 322mm
- TRG2FT:** 642mm
- TRG3FT:** 930mm
- TRG4FT:** 1217mm



Code	Version	Colour	Wattage	IP Rating
TH1	1 Ft Heater	White	60W	IP44
TH2	2 Ft Heater		120W	
TH3	3 Ft Heater		180W	
TH4	4 Ft Heater		240W	
TRG1FT	1 Ft Guard	White		
TRG2FT	2 Ft Guard			
TRG3FT	3 Ft Guard			
TRG4FT	4 Ft Guard			



Fixing clips included