

LCD Network Length Tester



Features

- Measures length of network cable and locate the open point
- Self-checking function and automatically compensate any change in battery capacity or ambient temperature
- LCD light assists use in dark corners
- Enables cable to be located even when totally concealed

Specifications

Main Function	: Test, Track and Measure Length of Network Cable
Display	: LCD with Backlight
Tracking Type	: RJ45
Testing Type	: RJ45
Power	: 9V Alkaline Battery (Not Included)
Warranty	: 1 Year

Technical Indexes

72-2975 Transmitter Specifications	
Indicator	LCD 53mm × 25mm with Backlight
Tone Frequency	225Hz
Max. Distance of Transmission	2 km
Max. Distance of Cable Map	1 km
Max. Working Current	Less than 70mA
Tone Mode	2 Tone Adjustable
Compatible Connectors	RJ45
Max. Signal Voltage	15Vp-p
Function & Faults LCD Display	LCD Display (Wiremap, Tone, Short, No Adapter, Low Battery)
Cable Map Indication	LCD (#1 - #8)
Shielded Indication	LCD (#9)
Voltage Protection	AC 60V/DC 42V
Battery Type	DC 9V (NEDA 1604/6F22 DC 9V × 1pc)
Dimension (L × W × D)	185mm × 80mm × 32mm

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk



LCD Network Length Tester



72-2975 Receiver Specifications	
Frequency	225kHz
The Max. working current	Less than 70mA
Ear Jack	1
LED Illumination	2
Battery Type	DC 9V (NEDA 1604/6F22 DC9V) ×1pc
Dimension (L × W × D)	218mm × 46mm × 29mm
72-2975 Remote unit specifications	
Compatible Connectors	RJ45
Dimension (L × W × D)	107mm × 30mm × 24mm

Attention

- Read the user manual before use it
- Do not connect high voltage lines to avoid burning out the machine
- Place the device in right place to avoid hurting others
- Connect the cable to the right port

Part Number Table

Description	Part Number
LCD Network Length Tester, RJ45 Port	72-2975

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell Limited 2016.

www.element14.com
www.farnell.com
www.newark.com
www.cpc.co.uk

