

TECHNICAL DATA SHEET



LAN Cable Model: CB11323

RoHS
Compliant

Design of cable:	
Inner conductor	Single bare copper 0.485mm dia ± 0.005 mm
Insulation	HDPE
Insulation Dia	0.85mm dia ± 0.05 mm
Core colours	WH-BU/BU WH-OG/OG WH-GN/GN WH-BN/BN
Jacket	PVC
Colour	Red
Size	4.8mm dia ± 0.2 mm
Wall thickness	≈ 0.5 mm
Printing	By request
Electric data at 20°C	
Conductor resistance	$< 110 \Omega/\text{km}$
Insulation resistance	$> 5000 \text{M}\Omega/\text{km}$
Testing voltage	wire/wire 50Hz 1min=1.5KV
Impedance	$100 \Omega \pm 15 \Omega$
Packing	305M/CTN
Temperature range	$-10^\circ\text{C} \sim 60^\circ\text{C}$

Important Notice : This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

