



### Main

|                           |   |
|---------------------------|---|
| Range                     | Acti 9  |
| Product name              | Acti 9 IHP  |
| Device short name         | IHP   |
| Product or component type | Programmable digital time switch                                |
| Device application        | Building  |
| Battery type              | Lithium   |
| Number of channels        | 1   |
| Provided equipment        | Programming kit<br>Memory key                                   |
| Language                  | Spanish<br>Portuguese<br>English<br>Italian<br>German<br>French |
| Colour tint               | White (RAL 9003)  |

### Complementary

|                                |   |
|--------------------------------|---|
| Power consumption in W         | 0.4 W   |
| Maximum switching current      | 16 A - 250 V AC pf = 1<br>4 A - 250 V AC pf = 0.6 |
| [Ue] rated operational voltage | 230 V[Sapce]( - 15...10 % ) AC 50/60 Hz           |
| Cycle duration                 | 24 hours + 7 days                                 |
| Maximum number of switchings   | 56  |
| Minimum interval duration      | 1 min   |
| Accuracy                       | +/- 0.5 s/day 25 °C                               |
| Display type                   | LCD   |
| Battery life                   | 10 yr   |
| Backup time                    | 10 years time and program saving                  |

|                         |  |
|-------------------------|--|
| Mounting support        | DIN rail   |
| 9 mm pitches            | 2  |
| Function available      | Operating hours counter<br>Automatic winter/summer time changeover |
| Type of setting         | Absence for holidays function<br>PIN code                          |
| Connections - terminals | Screwless terminals : 2 x 0.5...2.5 mm <sup>2</sup>                |
| Width                   | 18 mm  |
| Height                  | 90 mm  |
| Depth                   | 66 mm  |
| Product weight          | 0.09 kg  |

## Environment

|                                       |             |
|---------------------------------------|-------------|
| IP degree of protection               | IP20 B      |
| Ambient air temperature for operation | -25...55 °C |

## Offer Sustainability

|                                  |   |
|----------------------------------|---|
| Sustainable offer status         | Green Premium product   |
| RoHS (date code: YYWW)           | Compliant - since 1504 - Schneider Electric declaration of conformity<br><a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold<br><a href="#">Reference not containing SVHC above the threshold</a>                |
| Product environmental profile    | Available   |
| Product end of life instructions | Available   |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|