

Universe	Professional
Type	Lighting
Category	ATEX / HAZLOC headlamps
Subcategory	ATEX headlamps



## PIXA® 1 (ATEX)


The PIXA 1 is a rugged headlamp offering lighting that allows the user to work comfortably on tasks close at hand. CONSTANT LIGHTING technology: brightness does not decrease gradually as the batteries are drained. It meets ATEX zone 2/22 certification requirements for work in explosive environments.



Flood beam for close-range work.



Knob can be handled with gloves to facilitate use of the headlamp under any conditions.



Headlamp meeting ATEX zone 2/22 certification requirements for work in explosive environments.



Excellent resistance to falls, to impacts and to crushing.

---

**Short Description** Headlamp for use in ATEX zone 2/22 explosive environments, suitable for proximity lighting. 60 lumens

---

- Selling Points**
- Headlamp keeps hands free for work and can be:
    - worn on the head with the headband
    - attached to the helmet with a mounting plate (included)
    - placed on the ground
  - CONSTANT LIGHTING technology ensures brightness that does not gradually decrease as the battery drains
  - Lighting for professionals that is reliable, practical and durable:
    - two lighting modes (low and high)
    - mode for close-range work: comfortable flood beam for proximity vision
    - automatically switches to reserve mode when batteries are almost drained (signaled by blinking light)
    - rotating knob that is ergonomic, even with gloves
    - storage position helps protect the headlamp lens and prevents inadvertently turning it on
    - may be used in explosive environments
    - excellent resistance to falls (2 m), impacts, and crushing (80 kg)
    - comfortable and washable elastic headband
    - resistant to chemicals
  - ATEX zone 2/22 certified headlamp
- 

- Specification**
- Weight: 160g
  - Technology: CONSTANT LIGHTING
  - Beam pattern: flood
  - Energy: 2 AA/LR06 batteries (included)
  - Battery compatibility: rechargeable Ni-MH and lithium
  - Watertightness: IP 67 (waterproof to -1 meter for 30 minutes; no maintenance required after immersion)
- 

**Lighting performance**

Lighting technology	Lighting modes	Beam pattern	Brightness	Distance	Burn time	Reserve mode
CONSTANT LIGHTING	close-range work	flood	20 lm	10 m	16 h	10 lm for 6h30
	movement		60 lm	15 m	3h30	

# Specifications by reference

Reference(s)	E78AHB 2
	Certification(s) : CE, II 3 G Ex nA ic IIB T4 Gc, II 3 D Ex tc IIIB or IIIC T135° C Dc, room temperature: -30° C to +40° C
Color(s)	black/yellow
Made in	MY
Guarantee	3 years
Packing	1
Case quantity	36
EAN	3342540097612

---

**Accessory(ies)**      POCHE PIXA  
RUBBER  
PIXA headband  
PIXADAPT

---

**Related product(s)**      VERTEX® BEST  
ALVEO VENT  
PIXA® 1 (HAZLOC)