

Thermal anemometer operated with smartphone

testo 405i

Compact professional measuring instrument from the Testo Smart Probes series, for use with smartphones/tablets

Measurement of air flow velocity, temperature and volume flow

Easy configuration (dimensions and geometry) of the duct cross-section for determining volume flow

Measurement data analyzed and sent via testo Smart Probes App

Telescopic shaft, extendable up to 400 mm

Space-saving and easy to transport





The hot-wire anemometer testo 405i, in combination with a smartphone or tablet, is a compact measuring instrument for air flow velocities, temperatures and volume flows. Equipped with a telescopic shaft, extendable to 400 mm, it allows flexible applications in rooms and ducts. Via the testo Smart Probes App installed on the end device, users can comfortably read off their measurement values, configure volume flow measurements quickly and easily, and reliably determine timed and multi-point mean values.

The measurement protocols can then be directly sent as PDF or Excel files. In combination with the thermal hygrometer testo 605i, the testo 405i is suitable for determining cooling or heating performance.



Technical data/accessories

testo 405i testo 405i, thermal anemometer operated with smartphone, incl. batteries and calibration protocol Order no. 0560 1405



testo Smart Probes App

The App turns your smartphone/tablet into the display of the testo 405i. The operation of the measuring instrument as well as the display of the measurement values take place by Bluetooth via the Testo Smart Probes App on your smartphone or tablet – independently of the measurement location. In addition to this, you can use the App to create measurement reports, add photos and comments to these, and send them by e-mail. For iOS and Android.

Sensor type	Hot wire
Measuring range	0 to 30 m/s
Accuracy ±1 digit	±(0.1 m/s + 5 % of m.v.) (0 to 2 m/s) ±(0.3 m/s + 5 % of m.v.) (2 to 15 m/s)
Resolution	0.01 m/s
Sensor type	NTC
Measuring range	-20 to +60 °C
Accuracy ±1 digit	±0.5 °C
	0.1 °C

General technical data

Compatability	requires iOS 8.3 or newer / Android 4.3 or newer
	requires mobile end device with Bluetooth 4.0
Storage temperature	-20 to +60 °C
Operating temperature	-20 to +50 °C
Battery type	3 micro batteries AAA
Battery life	15 hrs
Dimensions	200 x 30 x 41 mm
	Telescope extendable to 400 mm

Accessories		Order no.	
testo Smart Case (VAC) for the storage and transport of testo 405i, testo 410i, testo 510i, testo 605i, testo 805i and testo 905i, dimensions 270 x 190 x 60 mm	0516 0260		
ISO calibration certificate flow velocity, two-point calibration, calibration points 5; 10 m/s 0520 0			
ISO calibration certificate flow velocity, hot-wire/vane anemometer, Pitot tube; calibration points 1; 2; 5; 10 m/s			