


		Conditions	
cell type:		NiMH	
cell size:		AAA	
nominal voltage:	1.2	V	
max. charge voltage:	1.5	V at standard charge (0.1C / 20°C)	
capacity			
nominal:	1100	mAh discharge at 0.2C	
minimum:	1050	mAh discharge at 0.2C	
	1000	mAh discharge at 1C	
		1.0V end discharge voltage	
		ta: 20°C	
max. continuous discharge current:	3000	mA ta: 0...45°C	
charge		current	time
standard charge:	110	mA 14....16hrs	
quick charge:	330	mA 4hrs	
fast charge:	1100	mA 1.1hrs	
recommended charge termination control parameters:	0...5	mV -ΔV (-delta V)	
	0.8...1	°C temperature rise per minute	
	45...50	°C TCO (temperature cut off)	
trickle charge current:	10...50	mA (recommended)	
continuous overcharge: (less than 1 year)	≤ 100	mA no conspicuous deformation no leakage	
internal resistance: (impedance)	≤ 35	mΩ at 1KHz battery fully charged	
life expectancy:	≥ 500	cycles acc. IEC standard	
self discharge			
charge retention:	≥ 60	% after 28 days storage at 20°C	
initial capacity:	≥ 380	mAh within 30 days after delivery discharge at 0.2C	
ambient temperature range:	0...45	°C standard charge	
	10...40	°C fast charge	
	0...45	°C discharge (≥1C)	
	- 20...65	°C discharge (<1C)	
	- 20...50	°C storage (≤1month)	
	- 20...40	°C storage (≤3months)	
	- 20...30	°C storage (≤12months)	
QCT1:	20/1000/40		
QCT2:	30/950/50		


mechanical specifications

cell dimensions			
diameter d1:		10.5 - 0.7	mm
diameter d2:	max.	3.8	mm
height h1:		44.5 - 1.5	mm
height h2:	min.	0.8	mm
weight:		13.5 ± 2	g
blister card dimensions:		123 x 85	mm
blister card weight (incl. batteries):		35	g




Diagrams


standard charge




fast charge



low rate discharge



high rate discharge



	ANSMANN Specifications for model:	AAA - 1100mAh
		2pcs blister package
	data sheet no. / part no.	5035222
	supplier no.	701372
	author / date	TG / 28.02.2018