



Main

Range of product	Harmony XVP Universal
Product or component type	Indicator bank
Beacon or indicator bank unit type	Audible unit
Mounting diameter	50 mm
Component name	XVPC
Noise level	55...85 dB at 1 m
[Us] rated supply voltage	24 V DC
Housing colour	Cream

Complementary

Signalling type	Continuous or intermittent buzzer
Assembly style	Customer assembly, up to 5 units
Connections - terminals	Screw clamp terminals: 1 x 1.5 mm ² with cable end
Marking	CE
[Ui] rated insulation voltage	250 V conforming to IEC 60947-1
Nominal voltage limit	0.85...1.1 Un conforming to IEC 60947-5-1
Current consumption	<= 15 mA
[Uimp] rated impulse withstand voltage	4 kV conforming to IEC 60947-1
Fundamental frequency	10 adjustable levels
CAD overall width	56 mm
CAD overall height	129 mm
CAD overall depth	56 mm
Product weight	0.153 kg

Environment

Product certifications	CULus
Standards	EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for storage	-40...70 °C
Ambient air temperature for operation	-25...50 °C
Electrical shock protection class	Class I on support tube conforming to IEC 61140

Class II on base unit conforming to IEC 61140

IP degree of protection

IP43 conforming to IEC 60529

Contractual warranty


Warranty period

18 months

Indicator Bank with Audible Unit

Dimensions


Below drawing shows an indicator bank with 1 audible stage and 1 illuminated stage. Select the number of stages according to the product characteristics in order to get b dimension.



Number of illuminated units	+ Audible	b in mm	b in in.
0	+ 1	129	5.08
1	+ 1	194	7.64
2	+ 1	256	10.08
3	+ 1	318	12.52
4	+ 1	380	14.96

Indicator Bank


Adjustment of Audible Signal for Buzzer



- 1 Volume adjustment potentiometer: 55...85 dB. Use either cross headed or flat tipped screwdriver.
- 2 Adjustment of type of audible signal according to position of 2 links. Use flat-nose pliers.

10 configurations are possible:

Conf.	Position of links and type of audible signal
1	
2	
3	
4	
5	
6	
7	
8	
9	

Conf.	Position of links and type of audible signal
10	<div style="display: flex; align-items: flex-start;"> <div style="margin-right: 20px;"> <p>5 ○ ○ 6</p> <p>⊖ ⊕</p> <p>1 ○ ○ 2</p> <p>⊖ ⊕</p> </div> <div>  <p>The graph shows a sawtooth waveform. The vertical axis is labeled 'Hz' with values 500 and 1200. The horizontal axis is labeled 's' with values 3.75 and 0.25. The signal starts at 500 Hz, rises linearly to 1200 Hz over a period of 3.75 s, then drops linearly back to 500 Hz over a period of 0.25 s, and repeats.</p> </div> </div>