Product data sheet Characteristics

XB4BVM1

white complete pilot light Ø22 plain lens with integral LED 230...240V

Product availability: Non-Stock - Not normally stocked in distribution facility



Main		
Range of product	Harmony XB4	
Product or component type	Complete pilot light	
Device short name	XB4	
Bezel material	Chromium plated metal	-
Fixing collar material	Zamak	
Mounting diameter	0.87 in (22 mm)	
Head type	Standard	
Sale per indivisible quantity	1	
Shape of signaling unit head	Round	
Cap/Operator or lens colour	White	
Operator additional information	With plain lens	
Light source	Protected LED	
Bulb base	Integral LED	
Light source colour	White	
[Us] rated supply voltage	230240 V AC, 50/60 Hz	

Complementary

Height	1.85 in (47 mm)	- 60
Width	1.18 in (30 mm)	- <u>t</u>
Depth	2.13 in (54 mm)	- pstiti
Terminals description ISO n°1	(X1-X2)PL	_ S
Product weight	0.18 lb(US) (0.08 kg)	led a
Resistance to high pressure washer	1015.26 psi (7000000 Pa) at 131 °F (55 °C),distance: 0.1 m	nten
Connections - terminals	Screw clamp terminals: <= 2 x 1.5 mm² with cable end conforming to EN/IEC 60947-1 Screw clamp terminals: 1 x 0.222 x 2.5 mm² without cable end conforming to EN/IEC 60947-1	l ton si no
[Ui] rated insulation voltage	250 V (degree of pollution: 3) conforming to EN 60947-1	ntatic
[Uimp] rated impulse withstand voltage	4 kV conforming to EN 60947-1	- dune
Signalling type	Steady	- ob si
Supply voltage limits	195264 V AC	- L
Current consumption	14 mA	_ mie
		₩

Service life	100000 h at rated voltage and 25 °C	
Surge withstand	1 kV conforming to IEC 61000-4-5	
Compatibility code	XB4	

Environment

Protective treatment	TH
Ambient air temperature for storage	-40158 °F (-4070 °C)
Ambient air temperature for operation	-40158 °F (-4070 °C)
Electrical shock protection class	Class I conforming to IEC 60536
IP degree of protection	IP69 IP67 IP66 conforming to IEC 60529 IP69K
NEMA degree of protection	NEMA 13 NEMA 4X
IK degree of protection	IK06 conforming to IEC 50102
Standards	EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 60947-5-4 EN/IEC 60947-5-5 JIS C 4520 UL 508 CSA C22.2 No 14
Product certifications	CSA UL listed
Vibration resistance	5 gn (f = 12500 Hz) conforming to IEC 60068-2-6
Shock resistance	30 gn (duration = 18 ms) half sine wave acceleration conforming to IEC 60068-2-27 50 gn (duration = 11 ms) half sine wave acceleration conforming to IEC 60068-2-27
Resistance to fast transients	2 kV conforming to IEC 61000-4-4
Resistance to electromagnetic fields	9.14 V/yd (10 V/m) conforming to IEC 61000-4-3
Resistance to electrostatic discharge	6 kV on contact (on metal parts) conforming to IEC 61000-4-2 8 kV in free air (in insulating parts) conforming to IEC 61000-4-2
Electromagnetic emission	Class B conforming to IEC 55011

Ordering and shipping details

Category	22468 - PUSHBUTTONS,22MM(METAL) NEW
Discount Schedule	CS2
GTIN	00785901914389
Nbr. of units in pkg.	1
Package weight(Lbs)	8.00000000000002E-2
Returnability	N
Country of origin	FR


Contractual warranty

Warranty period	18 months

Product data sheet Dimensions Drawings

XB4BVM1

Dimensions



e: clamping thickness: 1 to 6 mm / 0.04 to 0.24 in.

b: 30 mm / 1.18 in. c: 46.5 mm / 1.83 in.

XB4BVM1

Panel Cut-out for Pushbuttons, Switches and Pilot Lights (Finished Holes, Ready for Installation)

Connection by Screw Clamp Terminals or Plug-in Connectors or on Printed Circuit Board	Connection by Faston Connectors
(2)	(5)

- (1) (2) (3) (4) Diameter on finished panel or support
- 40 mm min. / 1.57 in. min.
- 30 mm min. / 1.18 in. min.
- Ø 22.5 mm / 0.89 in. recommended (Ø 22.3 mm $_0$ $^{+0.4}$ / 0.88 in. $_0$ $^{+0.016})$
- (5) (6) 45 mm min. / 1.78 in. min.
- 32 mm min. / 1.26 in. min.