



OPTIONS



VERSIONS

Type	Force N	Feed mm/s	Pitch of screw mm	Resolution $\mu\text{m}/\text{step}$	Current per Winding A	Resistance per Winding Ohm	Weight kg	Stroke „A“ mm	Housing Length „B“ mm	Length „A“ mm
L2818S0604-T5x5-A	30	100	5	25	0.67	5.6	0.26/0.39	25/50	44/69	31.5
L2818L0604-T5x5-A	60	140	5	25	0.67	9.2	0.34/0.39	25/50	44/69	50.5

ORDER IDENTIFIER



L2818S0604-T5x5-
 A25 = 25 mm Stroke „A“
 A50 = 50 mm Stroke „A“

CAUTION



The force and power ratings specified in the data sheets are based on a duty cycle of 10% to 20% and must be reduced for higher values. Moving against fixed end stops should be avoided.

DIMENSIONS (IN MM)

