



Manual Tensioning Tool for Cable ties with low profile head

MK10-SB up to 9.5 mm strap width

Features and Benefits

- Ideal for easy handling of entire HellermannTyton RPE and PE-Series cable ties
- Tensions and cuts off pre-looped cable ties flush at the head



MK10-SB.

TYPE	Strap Width max. (G)	Strap Thickness max.	Weight	Article-No.
MK10-SB	9.5	2.5	0.33 kg	110-10001

All dimensions in mm. Subject to technical changes.



For product specific approvals and specifications please refer to the Appendix.

Manual Tensioning Tool for Cable Ties, simple version

MK20 up to 4.8 mm strap width

MK21 up to 7.6 mm strap width

Features and Benefits

- Lightweight, ergonomic tools
- For tensioning and cutting HellermannTyton standard cable ties 4.8 - 7.6 mm wide
- MK20 and MK21 ideal for on-site assembly
- Mounted and pre-tensioned ties are cut off by twisting the tool



MK20, MK21.



Apply.



Tension.



Twist to cut.

TYPE	Strap Width max. (G)	Strap Thickness max.	Weight	Article-No.
MK20	4.8	1.5	0.05 kg	110-20006
MK21	7.6	2.5	0.05 kg	110-21016

All dimensions in mm. Subject to technical changes.