



JUNCTION BOX

HP 100-L



HP 100-L

Junction box

113 x 113 x 58 mm

Article number: 32690001

Junction box acc. to DIN EN 60670 (VDE 0606), $U_i=690V$, 7 recessed stepped nipples, seal range 5 - 21 mm, for terminals up to 10 mm²

Grey, without terminals

IP55

10²

IK07



690V
AC



Technical data

Measures

Width:	113 mm
Length:	113 mm
Height:	58 mm
Inner height:	32 mm
Inner width:	103.5 mm
Inner length:	103.5 mm

Material:

Box:	polypropylene, flame-retardant
Cover:	polypropylene, flame-retardant
material:	Polypropylene

Accessory

DMS M20/w - {M 20, weiss}

DMS M25/w - {M 25, weiss}

Abox 025/040 KLS-2,5²/4² - Terminal block

BST M20/sw - Ventilation seal

WK 060 KLS-6² - Terminal block

WK 100 KLS-10² - Terminal block

BST M20 - Ventilation seal

DMS M20 - Double-membrane seals

DMS M25 - Double-membrane seals

KVR M20-GDB/MGM - Cable gland

KVR M20-MGM - Cable gland

KVR M25-MGM - Cable gland

SNI M20 - Stepped nipple

SNI M25 - Stepped nipple



JUNCTION BOX

HP 100-L

Other attributes

Equipment:	None
Entries:	11
Rated cross section:	10 mm ²
Tackable:	No
Rated insulation voltage AC:	690 V
Explosion safety:	none
Functional integrity:	none
sealable:	No
Heavy metals-free:	Yes
PVC-free:	Yes
Silicone-free:	Yes
Ingress protection:	IP55 - acc. to EN 60529 / DIN VDE 0470-1
weatherproof:	No

Environmental attributes

Ambient temperature (min.):	-25 °C
Ambient temperature (max.):	40 °C
Ambient temperature (24 h):	35 °C
Max. rel. humidity at 25° C (short term):	95%
Max. rel. humidity at 40° C:	50%