

## Accessories

### VG 21 HQ MS68 11.5-15.5

**Weidmüller Interface GmbH & Co. KG**  
 Klingenbergstraße 16  
 D-32758 Detmold  
 Germany  
 Fon: +49 5231 14-0  
 Fax: +49 5231 14-292083  
 www.weidmueller.com



With blueglobe®, Weidmüller has introduced a cable gland from Pflitsch into its portfolio that convinces both in terms of reliability and functionality.

A large sealing range from 1.5 to 77 mm thanks to removable inlets with just 11 cable glands, highly effective sealing, excellent strain relief and a groove-guided upstream O-ring – these are the features of the blueglobe® cable glands which Weidmüller offers in brass and stainless steel.

The heart of the blueglobe® cable gland is the spherical seal insert that squeezes the cable gently and over a large area. This permanently avoids the incisive notch effect that is common with lamella systems.

#### General ordering data

Type	VG 21 HQ MS68 11.5-15.5
Order No.	<a href="#">1016100000</a>
Version	Heavy Duty Connectors, Accessories, Cable gland, Brass, nickel-plated
GTIN (EAN)	4032248725564
Qty.	1 pc(s).

**Data sheet**

**Accessories**  
**VG 21 HQ MS68 11.5-15.5**

**Weidmüller Interface GmbH & Co. KG**  
Klingenbergstraße 16  
D-32758 Detmold  
Germany  
Fon: +49 5231 14-0  
Fax: +49 5231 14-292083  
www.weidmueller.com

**Technical data**

**Dimensions and weights**

Net weight 37 g

**Temperatures**

Limit temperature -40 °C ... 130 °C

**General data**

AF size	30 mm	Cable diameter, max.	15.5 mm
Cable diameter, min.	11.5 mm	Cable gland	PG 21
Internal thread	PG 21	Material	Brass, nickel-plated
Protection degree	IP68	Sealing material	TPE
Size	HQ	Tightening torque, max.	15 Nm

**Classifications**

ETIM 3.0	EC000441	ETIM 4.0	EC000441
ETIM 5.0	EC000441	ETIM 6.0	EC000441
UNSPSC	30-21-18-01	eClass 5.1	27-14-91-09
eClass 6.2	27-14-91-09	eClass 7.1	27-14-91-09
eClass 8.1	27-14-91-09	eClass 9.0	27-14-44-32
eClass 9.1	27-14-44-32		

**Approvals**

Approvals



ROHS Conform

**Downloads**

Brochure/Catalogue	<a href="#">CAT 3 HDC 17/18 EN</a> <a href="#">CAT 5 ENCL 17/18 EN</a> <a href="#">FL FIELDWIRING EN</a>
Engineering Data	<a href="#">EPLAN, WSCAD</a>