

Insert strip - PABL 15X4 - 0808260

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Insert strip, Sheet, white, unlabeled, can be labeled with: Office printing systems, CMS-P1-PLOTTER, perforated, mounting type: insert, cable diameter range: 0.6 - 50 mm, lettering field size: 15 x 4 mm

Why buy this product

- PABL ... sheets are available for labeling with a laser printer
- Can be printed with CMS-P1-PLOTTER and office printers



Key Commercial Data

Packing unit	10 STK
Minimum order quantity	10 STK
GTIN	 4 017918 171544
GTIN	4017918171544
Weight per Piece (excluding packing)	13.750 g
Custom tariff number	39206219
Country of origin	Germany

Technical data

Dimensions

Length (b)	4 mm
Width (a)	15 mm
Cable diameter	0.6 mm ... 50 mm

Ambient conditions

Ambient temperature (operation)	-40 °C ... 100 °C
Recommended storage conditions	23 °C / 50 % relative humidity

General

Note	Print image may vary depending on laser printer
Color	white

Insert strip - PABL 15X4 - 0808260

Technical data

General

Components	free from silicone and halogen
Flammability rating according to UL 94	V0
Material	Polyester
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Number of individual labels	360
Number of individual labels per row	12
Test for substances that would hinder coating with paint or varnish	VW PV 3.10.7:2005-02
Result	Test passed
Test specification weathering-resistance	Following ISO 4892-2:2013-03
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN 60068-2-11:2000-02
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:2013-05
Climate level	AHT 1.0 S
Cycles	2
Condensation test result	Test passed
Foil strength	135 µm
Marking mounting type	insert

Standards and Regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Flammability rating according to UL 94	V0

Classifications

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137
eCl@ss 8.0	27400401
eCl@ss 9.0	27400629

ETIM

ETIM 2.0	EC000761
ETIM 3.0	EC000761
ETIM 4.0	EC000761

Insert strip - PABL 15X4 - 0808260

Classifications

ETIM

ETIM 5.0	EC001288
ETIM 6.0	EC001288

UNSPSC

UNSPSC 6.01	30211811
UNSPSC 7.0901	39121410
UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39131504