

# LIFT EQUIPMENT

SHOP/GARAGE

## 2 TON FLOOR JACK & SETS

- 4,000 lbs. capacity jack, maximum height 13", swivel casters for easy positioning. Heavy duty steel lifting arm. Lightweight for fast positioning. Tough enamel finish.
- Ratcheting style 4,000 lbs. capacity jack stands.
- 40" cool weave folding creeper, 350 lbs. capacity.



**W85028**  
See Seats and Creepers for more details.

Item #	IP	MP	PKG	Lift Range	Pumps (to max height)	Length	Width	Height
<b>W1606</b> Jack Only	1	1	CBX	Jacks 5-1/4 to 13"	42	17"	8"	5-1/2"
<b>W1605</b> Jack & Stands	1	1	CBX	Stands 10-3/4 to 16-3/8"	-	6-11/16"	6-15/16"	16-3/8"
<b>W85030</b> Jack, Stands & Cool Weave Creeper	1	1	CBX	Folding Creeper	Open	40"	18"	4-3/4"
					Folded	-	19-7/8"	18"

## FLOOR JACKS

- Swivel casters for easy positioning.
- Durable flanged steel frame.
- Great for cars and light duty trucks.

Rapid lift feature allows you to quickly raise jack into position under the vehicle.



**W1614**  
Carry handle included.



**W1612**



**W1616**



**W1611**  
Carry handle included.  
blow molded plastic case.



**W1640**

Carry handle included.



**W1617**

Item #	Capacity	IP	MP	PKG	Lift Range	Pumps (to max height)	Base	
							Length	Width
<b>W1614</b>	2 Ton	1	1	CBX	5-1/4 to 15-1/2"	45	17"	8"
<b>W1611</b> Blow Case	2-1/4 Ton	1	1	CBX	5-1/4 to 15-1/2"	45	17"	8"
<b>W1640</b>	2-1/2 Ton	1	1	CBX	5 to 15-1/2"	42	21-5/8"	8"
<b>W1612</b>	2-1/2 Ton	1	1	CBX	5 to 19-1/4"	22	28-3/4"	14"
<b>W1616</b> Rapid Lift	3 Ton	1	1	CBX	4-5/8 to 19-3/4"	21	27"	13-1/2"
<b>W1617</b>	3 Ton	1	1	CBX	5-1/2 to 21-1/4"	18	28-1/2"	13-5/8"