


HAND HELD CASES

2900 Series Sloped Cases


Scratch resistant desktop or hand-held enclosures with recess in lid. Ideal for mobile electronics that require a battery compartment.

- Lid, base and battery lid moulded in high grade ABS
- Lid mounted by four M3 machine screws
- Angled LCD Display area
- Sliding battery compartment lid
- Recess in lid for membrane keypads or overlays



SPECIFICATION	
Materials	Base, lid and battery lid in high grade ABS
Operating temperature	Resistant to temperatures of up to 85°C
Protection class	IP54
Standard colours	Grey or black. Ivory to order
Standard unit includes	Base & lid Battery compartment lid 4 x M3 machine screws 4 x rubber feet

BLACK	GREY	LENGTH	WIDTH	HEIGHT
BIM2901-BLK/BLK	BIM2901-GY/GY	165mm	87mm	24mm



2910 Series Mobile Cases


Functional hand-held ABS cases with recessed lid and a battery compartment.

- Lid and base moulded in high grade ABS
- Lid mounted by four M3 machine screws
- Snap-on battery compartment lid
- Battery compartment for two AA, AAA or one PP3 battery
- PCB pillars in base
- Recess in lid for membrane keypads or overlays



SPECIFICATION	
Materials	Base & lid and battery lid in high grade ABS UL94-V0
Operating temperature	Resistant to temperatures of up to 85°C
Protection class	IP54
Standard colours	Light grey similar to RAL 7035 or black similar to RAL 9004
Standard unit includes	Base & lid Battery compartment lid 4 x M3 machine screws 4 x self-tapping PCB screws

BLACK	GREY	LENGTH	WIDTH	HEIGHT
CHHMC01BK	CHHMC01GY	105mm	61mm	28mm
CHHMC02BK	CHHMC02GY	145mm	80mm	34mm



UNIVERSAL
ENCLOSURES

HAND
HELD
CASES

HEAVY
DUTY
ENCLOSURES

DIN
RAIL
ENCLOSURES

INTERFACE
SUPPORTS

ELECTRICAL
ENCLOSURES

DIECAST
& METAL
ENCLOSURES

DESKTOP &
INSTRUMENT
CASES

MULTI-PURPOSE
& POTTING
BOXES

19"
ENCLOSURES

19"
CABINETS

DEVELOPMENT
BOARD
ENCLOSURES

CUSTOM
SIZED
ENCLOSURES

FSPT/CUSTOM
SERVICES