




## Clamp-type test probe

### KLEPS 30



Product	KLEPS 30
description	Clamp-type test probe with rotating grip jaws and flexible shaft. The special form of the grip jaws allows clamping of pins and wires up to a maximum of 4mm diameter. 4mm diameter brass socket connection with side screw, grip jaws additionally tin-plated.
article-no. / *colour	9301131xx <div style="display: flex; justify-content: space-around; align-items: center;"> <div style="text-align: center;">  00 black         </div> <div style="text-align: center;">  01 red         </div> </div>
drawing	
technical data	
connection	4 mm socket (unsprung) screw terminal
rated voltage <sup>(1)</sup>	30 VAC / 60 VDC
measurement cat. acc. to IEC 61010	O <sup>(3)</sup>
rated current <sup>(1)</sup> (consider derating curve)	4 A
material socket	brass
housing material	PF
temperature range acc. To IEC61010 <sup>(2)</sup>	-25 °C to +70 °C
flammability class acc. to UL 94 (only valid for basic material of housing)	V-0
clamp type	rotating grip jaws, tin plated
clamping range	4 mm

4 mm system

standard	IEC 61010
----------	-----------

- <sup>(1)</sup> for normal environmental conditions -5°C to +40°C  
<sup>(2)</sup> contact the manufacturer for applications at deviating temperature ranges  
<sup>(3)</sup> Other circuits that are not directly connected to mains  
stand: 09.07.2018