



DIB-102

Order No.: 24.7060

Price upon request

PRODUCTINFOS

DI Boxes

For an optimum signal transmission from musical instruments to a mixer or amplifier. By using a transformer coupling, interferences due to matching problems, e.g. hum loops, are prevented to a large extent. Input and output are galvanically isolated.

For adapting line levels, please use units of the LTR series!

2-channel DI box

- 3-fold attenuation switch (0/-20/-40 dB) for each channel
- 1 ground lift switch for each channel
- 1 instrument feed-through output for each channel
- Wideband balancing transformer
- Robust metal housing

tools4music 02/2010

on the LSP-102, LC-31, FGA-102, FGA-202, DIB-102

"The DIB-12 from IMG Stage Line impresses by both the attractive price and the very stable housing. The frequency curve is exemplary."

"Recommendable and fit for on-the-road applications. An attractively priced little audio aid, perfect for the 'ever accompanying' tool case."

TECHNICAL SPECIFICATIONS

DIB-102

Type	DI box
Frequency range	15-30,000 Hz, ± 0 dB
Input impedance	50 k Ω
Output impedance	600 Ω , XLR 50 k Ω , jack
Transmission ratio	10:1
Admiss. ambient temp.	0-40 °C
Dimensions	148 x 50 x 130 mm
Weight	755 g
Inputs	2 x 6.3 mm jack, unbal. 2 x 6.3 mm jack, unbal.,
Outputs	par. out 2 x XLR, bal.

DIB-102

Width	148 mm
Height	50 mm
Depth	130 mm
Weight	