


DO NOT SCALE DRAWING



REVISION	
A	INITIAL DRAWING 17.9.15

Part Number	ØA Max	ØB Max	C Nom	D Max
DM3 - DSSSTWA - Z100	3.4	5.6	1.0	2.36
DM3.5 - DSSSTWA - Z100	3.9	6.1	1.0	2.36
DM4 - DSSSTWA - Z100	4.4	7.0	1.2	2.83
DM5 - DSSSTWA - Z100	5.4	8.8	1.6	3.78
DM6 - DSSSTWA - Z100	6.5	9.9	1.6	3.78
DM8 - DSSSTWA - Z100	8.5	12.7	2.0	4.72
DM10 - DSSSTWA - Z100	10.7	16.0	2.5	5.9
DM20 - DSSSTWA - Z100	21.2	30.6	4.5	10.6

NOTES:



DESIGN RIGHT. TR FASTENINGS LTD, 2003
 UNDER NO CIRCUMSTANCES MUST THIS
 DRAWING BE COPIED OR DISCLOSED
 WITHOUT FIRST OBTAINING WRITTEN
 AUTHORITY.

UNLESS OTHERWISE SPECIFIED:
 DIMENSIONS ARE IN MM (MILLIMETERS).
 SURFACE FINISH:
 TOLERANCES: ISO 2768-m
 ANGULAR $\pm 2^\circ$

	NAME	DATE
DRAWN	Darryl Wilson	17.09.15
CHK'D		
APPVD		

CUSTOMER PART NUMBER:
 N/A

MATERIAL:
 SPRING STEEL

HEAT TREATMENT:

FINISH:
 TC1D - Commercial Zinc/Clear Trivalent
 De-Embrittled

TITLE:
 Square Section Spring Washer DIN 7980

DRAWING NUMBER:
 TR32DSSSTWA-Z100 DIN7980

A4