25MHz TRUE DUAL CHANNEL ARBITRARY FUNCTION GENERATOR











Equivalent Dual-Channel Provides Augmented Value for Customers

GW Instek is launching AFG-2225, its first basic level dual-channel arbitrary function generator, which provides superior features in its class. Both channels are equipped with same characteristics to fit dual-signal applications such as differential or IQ signaling. The outstanding cost-performance value makes the AFG-2225 a practical instrument to accelerate the development process.

The major features for both channels include 10Vpp output amplitude; 25MHz frequency bandwidth with 1uHz resolution; built-in waveforms of Sine, Square, Ramp (Triangle) and Noise. As to the 1%–99% adjustable duty cycle of Square waveform can be used as pulse signal sources. For the arbitrary waveform, user can edit the 66 built-in waveforms or create a whole new one. Moreover, AFG-2225 carries features of AM/FM/PM/FSK/SUM Modulation, Sweep, Burst and Frequency Counter, which can be applied to various communication fields.

In addition to the intuitive and friendly user interface, the 3.5-inch color LCD displays the comprehensive operation information including the true waveform presented at the output. USB Host and Device interfaces are equipped to link the AFG-2225 with other devices, which provide the flexibility of waveform generation for more practical usages. With link to GW Instek GDS-series Digital Storage Oscilloscopes (DSOs), the waveforms of interest can be captured and reconstructed. User can also use the arbitrary waveform PC software to edit the waveform and then send to AFG-2225 directly, or save the waveform into flash drive and then transfer to AFG-2225.

Full-Functions equipped Dual-channel Signal Output Capability

In most two-channel signals applications, such as digital modulation and vehicle electronic simulation signals, the similar or identical waveform capabilities are required for both channel outputs. Unlike other dual-channel AFG in this class, AFG-2225 is fully equipped with equal capabilities on dual outputs. Most of dual-channel arbitrary waveform generators in this basic level cluster offer one major channel and one minor channel, in which the minor channel only provides less functions or inferior performances. This sort of non-full-function dual-channel AFGs can not meet the requirements of reality.

Correlated Functions of Dual-channel Outputs

The two channels can be used in either independent or correlated configuration. AFG-2225 provides three correlated functions which are Couple, Tracking and Phase functions. For Couple function, two signals with a ratio or offset in amplitude or frequency can be generated. One of two signals with adjustable offset frequency is an example which can form the two-tone signals for testing the third order inter-modulation distortion of an amplifier. With Tracking function, two differential signals with equal-frequency, equal-amplitude but inverted phase can be produced. Examples such as PECL, LVPECL and LVDS digital signals or automotive sensors like temperature, speed signals are all able to be simulated by tracking function. The Phase function is designed to create two signals with specified phase offset. When user wants to create two quadrature (sine and cosine) signals, the phase offset is set to be 90 degrees in the Phase function. In conclusion, compared with other arbitrary function generators only equipped with phase function, AFG-2225 provides great convenience to fulfill the various challenges coming from modern electronic industries.

High-flexibility of Arbitrary Waveforms Editing

AFG-2225 provides 120MSa/s sampling rate, 10-bit vertical resolution, 4k-point waveform length, and the maximum waveform repeated rate of 60MHz, regarded as an outstanding arbitrary waveform capability. There are four ways for AFG-2225 to generate customized arbitrary waveforms, which are editing waveform via PC software, point-by-point editing on the panel, loading CSV file and loading the captured waveform from GW Instek GDS-Series Oscilloscopes.

The PC software editing and point-by-point editing particularly provide the way to create the user-defined and post-modification waveform. CSV file loading capability allows AFG-2225 to produce the waveforms with complicated math operation result. Engineer can use PC math software to process the integral and then send the results in CSV format to AFG-2225. With the link to GW Instek GDS-series Digital Storage Oscilloscopes (DSOs), the waveforms of interest can be captured by DSO and then reconstructed by AFG-2225. User can capture the waveform during the operation and then reconstructed by AFG-2225 for further analysis or diagnosis in the laboratory. Thus, plus the dual-channel feature, numerous derivative applications of capturing signal can be achieved.

AFG-2225

FEATURES

- Wide Frequency Ranges From 1 μHz ~
 25MHz (sine wave)
- 1 µHz Resolution in Full Range
- Built-in Standard 120MSa/s, 10bit, 4k
 Points Arbitrary Function
 for Both Channels
- True Dual-Channel Output, CH2 Provides the Same Characteristics as CH1
- Dual-Channel Supports Couple, Tracking, Phase Operations
- 1% ~ 99% Adjustable Duty Cycle for Square Waveform
- Friendly User Interface for Easy Parameter Setting and Parameters Display
- Multiple Editing Methods to Edit Arbitrary Waveform Easily
- Built-in Standard AM/FM/PM/FSK/SUM/ Sweep/Burst and Frequency Counter
- USB Host/Device Interface for Remote Control and Waveform Editing



Front Panel

APPLICATIONS

- Power Supply/Transformer Simulations
- Traditional/Motor Power Applications
- Laboratory and Educational Research
- Pulse Signal as Trigger or Synchronization
- Automotive Electronics Applications



AFG-2225

W. V. E. C. D. V. E.			CH1	CH2
VAVEFORMS RITRARY FUNCTION	Samuel B.		Sine, Square, Ramp, Pulse, Noise, ARB	
ARTIKARY FUNCTION	Sample Rate Repetition Rate		120MSa/s 60MHz	
	Waveform Length		4k point	
	Amplitude Resolu Non-Volatile Memo		10 bit 4k points	
REQUENCY CHARACTERISTICS	Range	Sine/Square	1μHz ~ 25MHz	
	Ramp		1MHz	
	Resolution Accuracy Stability		1μHz ±20ppm	
		Aging	±1ppm, per 1 year	
OUTPUT CHARACTERISTICS	Tolerance Amplitude Range		≤1mHz 1mVpp~10Vpp(into 50Ω), 2mVpp~20Vpp(open-c	ireuit)
or enameralismes	Accuracy Resolution		1mVpp~5Vpp(into 50Ω)for 20MHz~25MHz; 2m\	
			±2% of setting ±1mVpp(at 1kHz) 1mV or 3digits	
		Flatness	±1% (0.1dB) ≤100kHz, ±3% (0.3 dB) ≤5MHz, ±59	% (0.4 dB) ≤12MHz, ±10%(0.9dB)≤25MHz
		Units	(sine wave relative to 1kHz) Vpp, Vrms, dBm	
	Offset Range		±5Vpk ac+dc(into 50Ω); ±10Vpk ac+dc(open circu	uit); ± 2.5 Vpk ac+dc(into 50Ω) for 20 MHz ~ 25 MHz
	Accuracy		±5Vpk ac+dc(open circuit) for 20MHz~25MHz 2% of setting + 5mV+ 0.5% of amplitude	
	Waveform Output Impedance		50Ω typical (fixed); >10MΩ (output disabled)	
Protection NE WAVE CHARACTERISTICS Harmonic Distortion			Short-circuit protected ; Overload relay auto matic	
TINE WAVE CHARACTERISTICS	Harmonic Distortion		≤-55 dBc, DC ~ 200kHz, Ampl > 0.1Vpp; ≤-50 dB ≤-35 dBc, 1MHz ~ 5MHz, Ampl > 0.1Vpp; ≤-30 d	ic, 200kHz ~ 1MHz, Ampl > 0.1Vpp IBc, 5MHz ~ 25MHz, Ampl > 0.1Vpp
QUARE WAVE CHARACTERISTICS	Rise/Fall Time		≤ 25ns at maximum output (into 50Ω load)	, , , , , , , , , , , , , , , , , , , ,
	Overshoot Asymmetry		5% 1% of period + 5 ns	
	Variable Duty Cycle		1% of period + 5 ns 1.0%~99%≤100kHz; 10.0%~90.0%≤1MHz; 50.0	0%≤25MHz
AMP CHARACTERISTICS	RISTICS Linearity		< 0.1% of peak output	
ULSE CHARACTERISTICS	Variable Symmetry		0%~100%(0.1% Resolution)	
ULSE CHARACTERISTICS	Period Pulse Width		40ns ~ 2000s 20ns ~ 1999.9s	
	Overshoot Jitter		<5% 20ppm + 5ns	
AM MODULATION	Carrier Waveforms		Sine, Square, Ramp, Pulse, Arb	Sine, Square, Ramp, Pulse, Arb
	Modulating Waveforms		Sine, Square, Triangle, Upramp, Dnramp	Sine, Square, Triangle, Upramp, Dnramp
	Modulating Frequency Depth		2mHz ~ 20kHz (INT); DC ~ 20kHz (EXT) 0% ~ 120.0%	2mHz ~ 20kHz (INT); DC ~ 20kHz (EXT) 0% ~ 120.0%
	Source		Internal / External	Internal / External
M MODULATION	Carrier Waveforms		Sine, Square, Ramp	Sine, Square, Ramp
	Modulating Waveforms Modulating Frequency		Sine, Square, Triangle, Upramp, Dnramp 2mHz ~ 20kHz (INT); DC ~ 20kHz (EXT)	Sine, Square, Triangle, Upramp, Dnramp 2mHz ~ 20kHz (INT); DC ~ 20kHz (EXT)
	Peak Deviation		DC ~ Max Frequency	DC ~ Max Frequency
	Source		Internal / External	Internal / External
М	Carrier Waveforms Modulating Waveforms		Sine, Square, Ramp Sine, Square, Triangle, Upramp, Dnramp	Sine, Square, Ramp Sine, Square, Triangle, Upramp, Dnramp
	Modulation Frequency		2mHz ~ 20kHz (INT); DC ~ 20kHz (EXT)	2mHz ~ 20kHz (INT); DC ~ 20kHz (EXT)
	Phase Deviation Source		0° ~ 360° Internal / External	0° ~ 360° Internal / External
SK	Carrier Waveforms		Sine, Square, Ramp, Pulse	Sine, Square, Ramp, Pulse
	Modulating Waveforms		50% duty cycle square	50% duty cycle square
	Modulation Frequency Phase Deviation		2mHz ~ 100 kHz (INT); DC ~ 100 kHz(EXT) 1μHz ~ Max Frequency	2mHz ~ 100 kHz (INT); DC ~ 100 kHz(EXT) 1μHz ~ Max Frequency
	Source		Internal / External	Internal / External
шм	Carrier Waveforms		Sine, Square, Ramp, Pulse, Noise	Sine, Square, Ramp, Pulse, Noise
	Modulating Waveforms Modulation Frequency		Sine, Square, Triangle, Upramp, Dnramp 2mHz ~ 20kHz (INT); DC ~ 20kHz (EXT)	Sine, Square, Triangle, Upramp, Dnramp 2mHz ~ 20kHz (INT); DC ~ 20kHz (EXT)
	Phase Deviation	icy	0% ~ 100.0%	0% ~ 100.0%
	Source		Internal / External	Internal / External
WEEP	Waveforms Type		Sine, Square, Ramp Linear or Logarithmic	Sine, Square, Ramp Linear or Logarithmic
	Start/Stop Freq		1μHz to Max Frequency	1μHz to Max Frequency
	Sweep Time Source		1ms ~ 500s Internal / External/Manual	1ms ~ 500s Internal / External/Manual
URST	Waveforms		Sine, Square, Ramp	Sine, Square, Ramp
	Frequency Burst Count		1μHz ~ 25MHz	1μHz ~ 25MHz
	Start/Stop Phase		1 ~ 65535 cycles or Infinite -360 ~ +360	1 ~ 65535 cycles or Infinite -360 ~ +360
	Internal Period		1ms ~ 500s	1ms ~ 500s
	Gate Source Trigger Source		External Trigger Single, External or Internal Rate	External Trigger Single, External or Internal Rate
	N-Cycle, Infinite		Os ~ 65535Ons	Os ~ 65535Ons
REQUENCY COUNTER	Range		5Hz ~ 150MHz	
	Accuracy Time Base		Time Base accuracy ± 1 count ± 20 ppm (23 °C ± 5 °C) after 30 minutes warm up	
	Resolution		The maximum resolution is: 100nHz for 1Hz, 0.1Hz for 100MHz	
	Input Impedance Sensitivity		1kΩ/1pf 35mVrms ~ 30Vms (5Hz ~ 150MHz)	
DUAL CHANNEL FUNCTION	Phase		-180° ~ 180°, Synchronize phase CH2=CH1	-180 $^{\circ}$ \sim 180 $^{\circ}$, Synchronize phase CH1=CH2
	Tracking Coupling		CH2=CH1 Frequency(Ratio or Difference)Amplitude & DC Offset	CH1=CH2 Frequency(Ratio or Difference)Amplitude & DC Offs
	DSOlink		✓	~
EXTERNAL TRIGGER INPUT	Туре		For FSK, Burst, Sweep	
	Input Level		TTL Compatibility Rising or Falling(Selectable)	
	Slope Pulse Width		>100ns	
	Input Impedance		10kΩ, DC coupled	
XTERNAL MODULATION INPUT	Type Voltage Range		For AM, FM, PM, SUM ±5V full scale	
	Input Impedance		10kΩ	
RIGGER OUTPUT	Frequency Type		DC ~ 20kHz	
RIGGER OUTFUT	Type Level		For Burst, Sweep, Arb TTL Compatible into 50Ω	
	Pulse Width		>450ns	
	Maximum Rate Fan-out		1MHz ≥4 TTL Load	
	Impedance		50Ω Typical	
ave/RECALL NTERFACE	10 Groups of Sett USB (Host & Devi			
	3.5" TFT LCD			
DISPLAY	AC100 ~ 240V , 5	0 ~ 60Hz		
DISPLAY POWER SOURCE	2E1V/ (* *)			
DISPLAY POWER SOURCE POWER CONSUMPTION	25W (Max.) Temperature to sa	tisfy the specifica	tion: 18~28°C; Operating temperature: 0~40°C; Relative	ve Humidity; ≤80%. 0~40°C; ≤70%. 35~40°C
DISPLAY OWER SOURCE OWER CONSUMPTION OPERATING ENVIRONMENT	Temperature to sa Installation catego		tion: 18~28°C; Operating temperature: 0~40°C; Relativ	ve Humidity: ≤80%, 0~40°C; ≤70%, 35~40°C;
DISPLAY OWER SOURCE OWER CONSUMPTION OPERATING ENVIRONMENT OPERATING ALTITUDE	Temperature to sa Installation catego 2000 meters	ory: CAT II	tion: 18~28°C; Operating temperature: 0~40°C; Relativ	ve Humidity: ≤80%, 0~40°C; ≤70%, 35~40°C;
DISPLAY OWER SOURCE OWER CONSUMPTION OPERATING ENVIRONMENT	Temperature to sa Installation catego	ory: CAT II		ve Humidity: ≤80%, 0~40°C; ≤70%, 35~40°C;

AFG-2225 25MHz True Dual Channel Arbitrary Function Generator User Manual CD \times 1, Quick Start Manual \times 1, GTL-101 Test Lead \times 2, Power Cord \times 1 GOOD WILL INSTRUMENT CO., LTD.
No.7-1, Jhongsing Road, Tucheng Dist., New Taipei City 236, Taiwan
T +886-2-2268-0389 F +886-2-2268-0639

