# **APPLICATIONS**



## **Front and Back Plates**

Front and back plates only for use with existing mortice latch or lock. The existing lock must have a fixing hole 22mm (1/8") below the follower (spindle).



#### Mortice Latch

Medium-duty tubular mortice latch locks. Stainless steel latchbolt head with 'anti-shim' deadlocking plunger, 8mm (5/16") follower. The outside lever handle will retract the latch after a correct code is entered. The spring loaded latchbolt will lock automatically when the door is closed.



#### **Mortice Lock**

Euro profile mortice sash lock with deadbolt and latchbolt. Complete with double cylinder to control deadbolt and to retract latchbolt. With the deadbolt locked it denies access to a code user. The split follower enables the inside lever to retract the deadbolt and latch to prevent accidental lock in when the deadbolt is thrown. Supplied with double Euro profile cylinders with three keys. The key will open the door for management functions.



# **Code Change Method**

Requires removal of lock from door. Locks are supplied with a random code commencing with the 'C' clear button. To change the code after fitting, the lock must first be removed from the door. The code is non sequential, i.e. the code can be entered in any preferred order (e.g. 1234 can be 4321 or 1342). A total of 8,191 different codes are available - any of which can be entered in any order.

## **OPTIONS**

#### **Latch Options:**

60mm (23/8") backset requires 25mm (1") hole, 82mm (31/4") deep. 70mm (2¾") backset requires 25mm (1") hole, 92mm (35/8") deep.

#### **Code Free Option:**

The outside lever will retract the latchbolt without using a code.

# Back to Back Option (BB):

Two coded plates for installation on both sides of the door. Provides coded access in both directions.


# For further product model options see price list.

# **PRODUCT DIMENSIONS**

# **CL410 CL400** 41mm (15/8") 000000 00000 50mm (5 %1e") 000 30mm (13/16") ōō 57mm (21/4") 60mm (23/8")

# 25mm (1")

**CL420** 



# **TECHNICAL SPECIFICATIONS**

Seven available
Two part 8mm (5/16") spring loaded spindle
Zinc Alloy
35mm - 60mm (1 <sup>3</sup> / <sub>8</sub> " - 2 <sup>3</sup> / <sub>8</sub> ")
14 stainless steel buttons
Locks will fit doors hung on the left or right
Vertical
PVD (Physical Vapour Deposition)
hardwearing low maintenance finishes
SS (stainless steel) and PB (polished brass)
8,191 non sequential codes available
Single Code
Codelocks Fire Kit Packs can be fitted to
latch locks for 30 or 60 minute fire doors.
Tested in accordance with:
BS EN 1634-1:2008
Internal and external use

\*Codelocks mechanical locks will be repaired, serviced or replaced free of charge if they develop a manufacturing fault. Faults caused by misuse, abuse and/or poor fitting are not covered by the guarantees.

















cluk2017v1