

DULUX T/E PLUS 26 W/840 GX24Q

OSRAM DULUX T/E PLUS | CFLni, 3 tubes, with 4-pin base for ECG operation



- Offices, public buildings
- Hotels, restaurants
- Industrial lighting
- Shops

Product benefits

- Very economical
- Good quality of light
- Excellent luminous flux
- Long service life
- OSRAM System+ Guarantee in combination with OSRAM QUICKTRONIC ECG
- Improved maintenance

Product features

- Average life: 20,000 h (with QUICKTRONIC)
- Color rendering index R_a : 80...89
- Dimmable (3...100 %)
- Short and compact pin-base lamp with triple-turn tubes
- Single-ended four-pin plug-in GX24q base with shortened base casing



Technical data

Electrical data


Nominal wattage	26 W
Rated lamp efficacy (HF data)	Under clarification by authority and standardization body
Rated lamp efficacy (standard condition)	68 lm/W
Rated wattage	26.5 W

Light technical data


Color rendering index Ra	>=80
Rated luminous flux	1800 lm
Luminous flux at 25 °C	1800 lm
Light color	840
Color temperature	4000 K
Nominal luminous flux	1800 lm
Light color as per EN 12464-1	LUMILUX Cool White
Rated LLMF at 2,000 h	0.89
Rated LLMF at 4,000 h	0.86
Rated LLMF at 6,000 h	0.84
Rated LLMF at 8,000 h	0.82
Rated LLMF at 12,000 h	0.79
Rated LLMF at 16,000 h	0.78
Rated LLMF at 20,000 h	0.76
Luminance	6 cd/cm ²

Dimensions & weight


Length	132.0 mm
Length acc. to IEC standard	130 mm
Length with base excl. base pins/connection	115.00 mm



Product line drawing with letters



Prod line drw, top, neutral dimensions



Base

Colors & materials

Lamp mercury content	2.6 mg
----------------------	--------

Temperatures

Rated ambient temp.w.max.luminous flux	25.0 °C
--	---------


Lifespan

Service life	13000 h ¹⁾
Rated lamp survival factor at 2,000 h	0.99
Rated lamp survival factor at 4,000 h	0.99
Rated lamp survival factor at 6,000 h	0.99
Rated lamp survival factor at 8,000 h	0.99
Rated lamp survival factor at 12,000 h	0.95
Rated lamp survival factor at 16,000 h	0.81
Rated lamp survival factor at 20,000 h	0.50
Operation mode LLMF/LSF	HF
Lifespan	20000 h ¹⁾

¹⁾ With preheat ECG

Additional product data

Base (standard designation)	GX24q-3
Appropriate disposal acc. to WEEE	Yes



Spectral power distribution

Capabilities

Suitable for indoor	Yes
---------------------	-----

Certificates & standards

EEI – Energy Label	B
--------------------	---

Country specific categorizations

UK Org	DTE264
--------	--------

Lamp-ECG combination (System)

QT-ECO 1x26/220-240 S

Products

QT-ECO 1x26/220-240 S

QT-ECO T/E 2x26/220-240

Products

QT-ECO T/E 2x26/220-240

QT-M 2x26-42/220-240 S

Products

QT-M 2x26-42/220-240 S

QTP-M 1x26-42

Products

QTP-M 1x26-42

QTP-M 2x26-32

Products

QTP-M 2x26-32

QTP-T/E (1x26-42), 2x26

Products

QTP-T/E 1x26-42, 2x26

QTP-T/E 1x26-42, (2x26)

Products

QTP-T/E 1x26-42, 2x26

QTi DALI-T/E 1x18-57 DIM

Products

QTi DALI-T/E 1x18-57 DIM

QTi DALI-T/E 2x18-42 DIM

Products

QTi DALI-T/E 2x18-42 DIM

QTi-T/E 1x18-57 DIM

Products

QTi-T/E 1x18-57 DIM

QTi-T/E 2x18-42 DIM

Products



QTi-T/E 2x18-42 DIM

Equipment / Accessories

- Suitable for operation on electronic control gear


Safety advice

In case of lamp breakage: www.osram.com/brokenlamp



Circuit diagram

Circuit diagram



Circuit diagram

Logistical Data

Product code	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Gross weight	Volume
4050300342283	Folding carton box 1	49 mm x 46 mm x 144 mm	74.00 g	0.32 dm ³
4050300342290	Shipping carton box 10	116 mm x 159 mm x 260 mm	853.00 g	4.80 dm ³

References / Links

For more information on QUICKTRONIC electronic control gear go to

▶ www.osram.com/QUICKTRONIC

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.