




Thermocouple Cable PTFE Insulated Twin Twisted Pair



- ◆ PTFE twin twisted pair for extending or making simple thermocouples
- ◆ Single pair of PTFE insulated conductors twisted together
- ◆ Thermocouple types K, J & T with 1/0.2mm conductors
- ◆ Good mechanical strength and flexibility, resistant to oils, acids and other adverse fluids
- ◆ Suitable for steam & pressure applications, autoclaves, sterilizers etc.
- ◆ 25, 50 & 100 metre reel lengths
- ◆ Tolerance Class 1 for optimum accuracy
- ◆ Insulation rating -75°C to 260°C
- ◆ Colour coded to IEC-584-3

T/C Type	Conductors	mm ²	Cores	Reel Length	Manufacturers Part No.
K	1/0.2mm	0.032	+Green/-White	25m	XF-243-FAR
K	1/0.2mm	0.032	+Green/-White	50m	WK-200X50
K	1/0.2mm	0.032	+Green/-White	100m	WK-200X100
J	1/0.2mm	0.032	+Black/-White	25m	XF-242-FAR
T	1/0.2mm	0.032	+Brown/-White	25m	XF-244-FAR
T	1/0.2mm	0.032	+Brown/-White	50m	WT-300X50
T	1/0.2mm	0.032	+Brown/-White	100m	WT-300X100

About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com

