

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name : Jetcem Rapid Set Cement

1.2 Relevant identified uses of the substance or mixture and uses advised against

At present there is no complete information available on identified uses. When the data becomes available, it will be integrated into the safety data sheet.

1.3 Details of the supplier of the safety data sheet

Company : Everbuild Building products LTD
Site 41, Knowsthorpe Way
Cross Green Industrial Estate
Leeds
LS9 OSW
UK

Telephone : 0113 240 3456

E-mail address : sds@everbuild.co.uk

1.4 Emergency telephone number

Emergency telephone number : 0044 113 240 3456 (office hours only)

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Type of product : Mixture

Classification (REGULATION (EC) No 1272/2008)

Serious eye damage, Category 1 H318: Causes serious eye damage.

Classification (67/548/EEC, 1999/45/EC)

Irritant R41: Risk of serious damage to eyes.

2.2 Label elements

Labelling (REGULATION (EC) No 1272/2008)

Hazard pictograms :



Signal word : Danger

Hazard statements : H318 Causes serious eye damage.

Precautionary statements : **Prevention:**
 P280 Wear protective gloves/ eye protection/ face protection.

Response:
 P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P310 Immediately call a POISON CENTER or doctor/ physician.

Hazardous components which must be listed on the label:

- 266-043-4 Cement, portland, chemicals

2.3 Other hazards

This mixture contains no substance considered to be persistent, bioaccumulating and toxic (PBT).
 This mixture contains no substance considered to be very persistent and very bioaccumulating (vPvB).

SECTION 3: Composition/information on ingredients

3.2 Mixtures

Hazardous components

Chemical Name CAS-No. EC-No. Registration number	Classification (67/548/EEC)	Classification (REGULATION (EC) No 1272/2008)	Concentration [%]
Cement, portland, chemicals 65997-15-1 266-043-4	Xi; R41	Eye Dam.1; H318	>= 25 - < 50
Substances with a workplace exposure limit :			
Quartz (SiO ₂) 14808-60-7 238-878-4			>= 50 - <= 100

For the full text of the R-phrases mentioned in this Section, see Section 16.
 For the full text of the H-Statements mentioned in this Section, see Section 16.

SECTION 4: First aid measures

4.1 Description of first aid measures

General advice : Move out of dangerous area.
 Consult a physician.
 Show this safety data sheet to the doctor in attendance.

If inhaled : Move to fresh air.
 Consult a physician after significant exposure.

- In case of skin contact : Take off contaminated clothing and shoes immediately.
Wash off with soap and plenty of water.
If symptoms persist, call a physician.
- In case of eye contact : Small amounts splashed into eyes can cause irreversible tissue damage and blindness.
In the case of contact with eyes, rinse immediately with plenty of water and seek medical advice.
Continue rinsing eyes during transport to hospital.
Remove contact lenses.
Keep eye wide open while rinsing.
- If swallowed : Clean mouth with water and drink afterwards plenty of water.
Do not give milk or alcoholic beverages.
Never give anything by mouth to an unconscious person.

4.2 Most important symptoms and effects, both acute and delayed

- Symptoms : Excessive lachrymation
See Section 11 for more detailed information on health effects and symptoms.
- Risks : No known significant effects or hazards.

4.3 Indication of any immediate medical attention and special treatment needed

- Treatment : Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

- Suitable extinguishing media : Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

5.2 Special hazards arising from the substance or mixture

- Hazardous combustion products : No hazardous combustion products are known

5.3 Advice for firefighters

- Special protective equipment for firefighters : In the event of fire, wear self-contained breathing apparatus.
- Further information : Standard procedure for chemical fires.

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

- Personal precautions : Use personal protective equipment.
Avoid breathing dust.

Deny access to unprotected persons.

6.2 Environmental precautions

Environmental precautions : Try to prevent the material from entering drains or water courses.

6.3 Methods and materials for containment and cleaning up

Methods for cleaning up : Pick up and arrange disposal without creating dust.
Keep in suitable, closed containers for disposal.

6.4 Reference to other sections

For personal protection see section 8.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advice on safe handling : Avoid exceeding the given occupational exposure limits (see section 8). Do not get in eyes, on skin, or on clothing. For personal protection see section 8. Smoking, eating and drinking should be prohibited in the application area. Follow standard hygiene measures when handling chemical products

Advice on protection against fire and explosion : Avoid dust formation. Provide appropriate exhaust ventilation at places where dust is formed.

Hygiene measures : Handle in accordance with good industrial hygiene and safety practice. When using do not eat or drink. When using do not smoke. Wash hands before breaks and at the end of workday.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storage areas and containers : Keep container tightly closed in a dry and well-ventilated place. Store in accordance with local regulations.

Other data : Keep in a dry place. No decomposition if stored and applied as directed.

7.3 Specific end use(s)

Specific use(s) : No data available

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Components with workplace control parameters

Components	CAS-No.	Value	Control parameters *	Basis *
Quartz (SiO ₂)	14808-60-7	TWA	0,1 mg/m ³	GB EH40
		TWA	0,1 mg/m ³	GB EH40
Cement, portland, chemicals	65997-15-1	TWA	10 mg/m ³	GB EH40
		TWA	4 mg/m ³	GB EH40

8.2 Exposure controls

Personal protective equipment

- Eye protection : Safety glasses with side-shields
 Eye wash bottle with pure water
- Hand protection : Chemical-resistant, impervious gloves complying with an approved standard must be worn at all times when handling chemical products. Reference number EN 374. Follow manufacturer specifications.
- Recommended: Butyl rubber/nitrile rubber gloves.
 Contaminated gloves should be removed.
- Skin and body protection : Dust impervious protective suit
 Protective clothing (e.g. Safety shoes acc. to EN ISO 20345, long-sleeved working clothing, long trousers). Rubber aprons and protective boots are additionally recommended for mixing and stirring work.
- Respiratory protection : Respirator selection must be based on known or anticipated exposure levels, the hazards of the product and the safe working limits of the selected respirator.
 particulate filter P
 P1: Inert material; P2: Xn; P3: T, T+
 Ensure adequate ventilation. This can be achieved by local exhaust extraction or by general ventilation. (EN 689 - Methods for determining inhalation exposure). This applies in particular to the mixing / stirring area. In case this is not sufficient to keep the concentrations under the occupational exposure limits then respiration protection measures must be used.

Environmental exposure controls

- General advice : Try to prevent the material from entering drains or water courses.

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance	: powder
Colour	: grey
Odour	: No data available
Odour Threshold	: No data available
Flash point	: Note: Not applicable
Ignition temperature	: No data available
Lower explosion limit (Vol%)	: No data available
Upper explosion limit (Vol%)	: No data available
Flammability (solid, gas)	: No data available
Oxidizing properties	: No data available
Auto-ignition temperature	: No data available
pH	: No data available
Melting point/range / Freezing point	: No data available
Boiling point/boiling range	: No data available
Vapour pressure	: No data available
Density	: 1,30 g/cm ³ at 20 °C
Water solubility	: Note: Not applicable
Partition coefficient: n-octanol/water	: No data available
Viscosity, dynamic	: No data available
Viscosity, kinematic	: Note: Not applicable
Relative vapour density	: No data available
Evaporation rate	: No data available

9.2 Other information

No data available

SECTION 10: Stability and reactivity

10.1 Reactivity

No dangerous reaction known under conditions of normal use.

10.2 Chemical stability

The product is chemically stable.

10.3 Possibility of hazardous reactions

Hazardous reactions : Stable under recommended storage conditions.

10.4 Conditions to avoid

Conditions to avoid : No data available

10.5 Incompatible materials

Materials to avoid : No data available

10.6 Hazardous decomposition products

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Skin corrosion/irritation

Product:

Remarks: No data available

Serious eye damage/eye irritation

Product:

Remarks: Causes serious eye damage.

Respiratory or skin sensitisation

Product:

Remarks: No data available

Germ cell mutagenicity

Product:

Germ cell mutagenicity- Assessment : No data available

Carcinogenicity

Product:

Carcinogenicity - Assessment : No data available

ment

Reproductive toxicity

Product:

Reproductive toxicity - Assessment : No data available

No data available

SECTION 12: Ecological information

12.1 Toxicity

No data available

12.2 Persistence and degradability

No data available

12.3 Bioaccumulative potential

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

Product:

Assessment : This substance/mixture contains no components considered to be either persistent, bioaccumulative and toxic (PBT), or very persistent and very bioaccumulative (vPvB) at levels of 0.1% or higher.

12.6 Other adverse effects

No data available

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product : The generation of waste should be avoided or minimized wherever possible.
Empty containers or liners may retain some product residues. This material and its container must be disposed of in a safe way.
Dispose of surplus and non-recyclable products via a licensed waste disposal contractor.
Disposal of this product, solutions and any by-products should at all times comply with the requirements of environmental protection and waste disposal legislation and any regional local authority requirements.

Avoid dispersal of spilled material and runoff and contact with soil, waterways, drains and sewers.

Contaminated packaging : 15 01 10* packaging containing residues of or contaminated by dangerous substances

SECTION 14: Transport information

ADR

Not dangerous goods

IATA

Not dangerous goods

IMDG

Not dangerous goods

14.6 Special precautions for user

No data available

14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

Not applicable

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

Labelling according to EC Directives (1999/45/EC)

Hazard pictograms :



Irritant

R-phrases : R41 Risk of serious damage to eyes.

S-phrases : S26 In case of contact with eyes, rinse immediately with plenty of water and seek medical advice.

S39 Wear eye/face protection.

Prohibition/Restriction

REACH - Restrictions on the manufacture, placing on the market and use of certain dangerous substances, preparations and articles (Annex XVII) : Not applicable

REACH - Candidate List of Substances of Very High Concern for Authorisation (Article 59). : None of the components are listed (=> 0.1 %).

REACH - List of substances subject to authorisation : Not applicable

(Annex XIV)

REACH Information: All substances contained in our Products are
- preregistered or registered by our upstream suppliers, and/or
- preregistered or registered by us, and/or
- excluded from the regulation, and/or
- exempted from the registration.

VOC-CH (VOCV) : no VOC duties

VOC-EU (solvent) : Not applicable

If other regulatory information applies that is not already provided elsewhere in the Safety Data Sheet, then it is described in this subsection.

Health, safety and environmental regulation/legislation specific for the substance or mixture: : The Chemicals (Hazard Information and Packaging for Supply) Regulations 2002
Control of Substances Hazardous to Health Regulations 2002
The Management of Health and Safety at Work Regulations 1999
Health and Safety at Work Act 1974
Environmental Protection Act 1990 & Subsidiary Regulations

Other regulations : This product contains cement. Wet cement or mortar may cause alkali burns if in direct and/or prolonged contact with the skin. Wear protective clothing at all times when working with cement based products.

15.2 Chemical Safety Assessment

This product contains substances for which Chemical Safety Assessments are still required.

SECTION 16: Other information

Full text of R-Phrases

R41 Risk of serious damage to eyes.

Full text of H-Statements

H318 Causes serious eye damage.

Full text of other abbreviations

Eye Dam. Serious eye damage

The information contained in this Safety Data Sheet corresponds to our level of knowledge at the time of publication. All warranties are excluded. Our most current General Sales Conditions shall apply. Please consult the product data sheet prior to any use and processing.



Changes as compared to previous version !

