

M12 PCB receptacle male a-coded 8pol.



Part number	21 03 321 1818
Specification	M12 PCB receptacle male a-coded 8pol.
HARTING eCatalogue	https://b2b.harting.com/21033211818

Identification

Category	Connector
Series	Circular connectors M12
Element	PCB adapter
Specification	Straight

Version

Termination method	Reflow soldering termination (THR/SMC)
Gender	Male
Shielding	Shielded
Number of contacts	8
Coding	A-coding

Technical characteristics

Rated current	2 A
Rated voltage	30 V
Rated impulse voltage	1.5 kV
Pollution degree	3
Insulation resistance	$\geq 10^8 \Omega$
Contact resistance	$\leq 10 \text{ m}\Omega$
Ambient temperature	-40 ... +85 °C -5 ... +50 °C During connection
Mating cycles	≥ 100
Overvoltage category	III
Isolation group	I ($600 \leq \text{CTI}$)

Material properties

Material (insert)	LCP
Material (contacts)	Copper alloy
Surface (contacts)	Gold plated



Pushing Performance

Material properties

RoHS	compliant with exemption
RoHS exemptions	6c: Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	No
REACH ANNEX XIV substances	No
REACH SVHC substances	Yes
REACH SVHC substances	Lead

Specifications and approvals

UL / CSA	UL 1977 ECBT2.E102079 CSA-C22.2 No. 182.3 ECBT8.E102079
----------	--

Commercial data

Packaging size	1
Net weight	12.22 g
Country of origin	Germany
Customs tariff number	85366990