

SAFETY DATA SHEET
P18 EVERBUILD GAS LEAK DETECTOR

Page: 1
Compilation date: 18/11/14
Revision No: 2

Section 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name: P18 EVERBUILD GAS LEAK DETECTOR

1.2. Relevant identified uses of the substance or mixture and uses advised against

1.3. Details of the supplier of the safety data sheet

Company name: EVERBUILD BUILDING PRODUCTS LTD

SITE 41, KNOWSTHORPE WAY

CROSS GREEN INDUSTRIAL ESTATE

LEEDS

WEST YORKSHIRE

LS9OSW

ENGLAND

Tel: 0044 113 240 3456

Fax: 0044 113 240 0024

Email: sds@everbuild.co.uk

1.4. Emergency telephone number

Emergency tel: 0044 113 240 3456 (office hours only)

Section 2: Hazards identification

2.1. Classification of the substance or mixture

Classification under CLP: Eye Irrit. 2: H319

Classification under CHIP: This product has no classification under CHIP.

2.2. Label elements

Label elements under CLP:

Hazard statements: H319: Causes serious eye irritation.

Signal words: Warning

Hazard pictograms: GHS07: Exclamation mark



Precautionary statements: P264: Wash hands thoroughly after handling.

P501: Dispose of contents/container to in accordance with local regulations.

P280: Wear protective gloves/protective clothing/eye protection/face protection.

P410+412: Protect from sunlight. Do not expose to temperatures exceeding 50 °C.

P261: Avoid breathing vapours.

SAFETY DATA SHEET

P18 EVERBUILD GAS LEAK DETECTOR

Page: 2

P210: Keep away from heat/sparks/open flames/hot surfaces. - No smoking.

P251: Pressurized container: Do not pierce or burn, even after use.

P305+351+338: IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.

P337+313: If eye irritation persists: Get medical attention.

2.3. Other hazards

PBT: This product is not identified as a PBT/vPvB substance.

Section 3: Composition/information on ingredients

3.2. Mixtures

Hazardous ingredients:

SODIUM LAROYL SARCOSINATE

EINECS	CAS	CHIP Classification	CLP Classification	Percent
205-281-5	137-16-6	Xi: R38	-	1-10%

COCONUT DIETHANOLAMIDE

271-657-0	68603-42-9	Xi: R38; Xi: R41	Skin Irrit. 2: H315; Eye Dam. 1: H318; Aquatic Chronic 2: H411	1-10%
-----------	------------	------------------	--	-------

SODIUM NITRITE

231-555-9	7632-00-0	O: R8; T: R25; N: R50	Ox. Sol. 3: H272; Acute Tox. 3: H301; Aquatic Acute 1: H400	<1%
-----------	-----------	-----------------------	---	-----

Section 4: First aid measures

4.1. Description of first aid measures

Skin contact: Wash immediately with plenty of soap and water.

Eye contact: Bathe the eye with running water for 15 minutes. Consult a doctor.

Ingestion: Wash out mouth with water.

Inhalation: Move to fresh air in case of accidental inhalation of vapours. Consult a doctor.

4.2. Most important symptoms and effects, both acute and delayed

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: Drowsiness or mental confusion may occur.

4.3. Indication of any immediate medical attention and special treatment needed

Immediate / special treatment: Not applicable.

Section 5: Fire-fighting measures

[cont...]

SAFETY DATA SHEET
P18 EVERBUILD GAS LEAK DETECTOR

Page: 3

5.1. Extinguishing media

Extinguishing media: Suitable extinguishing media for the surrounding fire should be used. Use water spray to cool containers.

5.2. Special hazards arising from the substance or mixture

Exposure hazards: In combustion emits toxic fumes.

5.3. Advice for fire-fighters

Advice for fire-fighters: Wear self-contained breathing apparatus. Wear protective clothing to prevent contact with skin and eyes. Cool containers at risk with water spray jet.

Section 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions: Refer to section 8 of SDS for personal protection details. Turn leaking containers leak-side up to prevent the escape of liquid.

6.2. Environmental precautions

Environmental precautions: Do not discharge into drains or rivers. Contain the spillage using bunding.

6.3. Methods and material for containment and cleaning up

Clean-up procedures: Absorb into dry earth or sand. Transfer to a closable, labelled salvage container for disposal by an appropriate method.

6.4. Reference to other sections

Reference to other sections: Refer to section 8 of SDS.

Section 7: Handling and storage

7.1. Precautions for safe handling

Handling requirements: Avoid direct contact with the substance. Contact with skin and eyes can cause freeze burns

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions: Store in cool, well ventilated area. Keep container tightly closed.

Suitable packaging: Must only be kept in original packaging.

7.3. Specific end use(s)

Specific end use(s): No data available.

Section 8: Exposure controls/personal protection

8.1. Control parameters

Workplace exposure limits: No data available.

DNEL/PNEC Values

DNEL / PNEC No data available.

[cont...]

SAFETY DATA SHEET
P18 EVERBUILD GAS LEAK DETECTOR

Page: 4

8.2. Exposure controls

Engineering measures: Ensure there is sufficient ventilation of the area.

Respiratory protection: Self-contained breathing apparatus must be available in case of emergency.

Hand protection: Protective gloves.

Eye protection: Safety glasses. Ensure eye bath is to hand.

Skin protection: Protective clothing.

Section 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

State: Liquified gas

Colour: Colourless

Odour: Barely perceptible odour

Solubility in water: Slightly soluble

Boiling point/range°C: 100

Relative density: 1.02

9.2. Other information

Other information: No data available.

Section 10: Stability and reactivity

10.1. Reactivity

Reactivity: Stable under recommended transport or storage conditions.

10.2. Chemical stability

Chemical stability: Stable under normal conditions.

10.3. Possibility of hazardous reactions

Hazardous reactions: Hazardous reactions will not occur under normal transport or storage conditions.

Decomposition may occur on exposure to conditions or materials listed below.

10.4. Conditions to avoid

Conditions to avoid: Heat.

10.5. Incompatible materials

Materials to avoid: Strong oxidising agents. Strong acids.

10.6. Hazardous decomposition products

Haz. decomp. products: In combustion emits toxic fumes.

Section 11: Toxicological information

11.1. Information on toxicological effects

[cont...]

SAFETY DATA SHEET
P18 EVERBUILD GAS LEAK DETECTOR

Page: 5

Hazardous ingredients:

SODIUM NITRITE

ORL	MUS	LD50	175	mg/kg
ORL	RAT	LD50	180	mg/kg
SCU	RAT	LD50	96600	µg/kg

Toxicity values: No data available.

Symptoms / routes of exposure

Skin contact: There may be mild irritation at the site of contact.

Eye contact: There may be irritation and redness.

Ingestion: There may be irritation of the throat.

Inhalation: Drowsiness or mental confusion may occur.

Section 12: Ecological information

12.1. Toxicity

Ecotoxicity values: No data available.

12.2. Persistence and degradability

Persistence and degradability: Biodegradable.

12.3. Bioaccumulative potential

Bioaccumulative potential: No bioaccumulation potential.

12.4. Mobility in soil

Mobility: Readily absorbed into soil.

12.5. Results of PBT and vPvB assessment

PBT identification: This product is not identified as a PBT/vPvB substance.

12.6. Other adverse effects

Other adverse effects: Negligible ecotoxicity.

Section 13: Disposal considerations

13.1. Waste treatment methods

Disposal operations: Dispose of according to local or national legislation

Waste code number: 16 05 04

NB: The user's attention is drawn to the possible existence of regional or national regulations regarding disposal.

Section 14: Transport information

14.1. UN number

UN number: UN1950

[cont...]

SAFETY DATA SHEET
P18 EVERBUILD GAS LEAK DETECTOR

Page: 6

14.2. UN proper shipping name

Shipping name: AEROSOLS

14.3. Transport hazard class(es)

Transport class: 2

14.4. Packing group

14.5. Environmental hazards

Environmentally hazardous: No

Marine pollutant: No

14.6. Special precautions for user

Special precautions: No special precautions.

Tunnel code: D

Section 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

15.2. Chemical Safety Assessment

Section 16: Other information

Other information

Other information: This safety data sheet is prepared in accordance with Commission Regulation (EU) No 453/2010.

* indicates text in the SDS which has changed since the last revision.

Phrases used in s.2 and s.3: H272: May intensify fire; oxidiser.

H301: Toxic if swallowed.

H315: Causes skin irritation.

H318: Causes serious eye damage.

H319: Causes serious eye irritation.

H400: Very toxic to aquatic life.

H411: Toxic to aquatic life with long lasting effects.

R8: Contact with combustible material may cause fire.

R25: Toxic if swallowed.

R38: Irritating to skin.

R41: Risk of serious damage to eyes.

R50: Very toxic to aquatic organisms.

Legend to abbreviations: PNEC = predicted no effect level

DNEL = derived no effect level

LD50 = median lethal dose

LC50 = median lethal concentration

EC50 = median effective concentration

[cont...]

SAFETY DATA SHEET
P18 EVERBUILD GAS LEAK DETECTOR

Page: 7

IC50 = median inhibitory concentration

dw = dry weight

bw = body weight

cc = closed cup

oc = open cup

MUS = mouse

GPG = guinea pig

RBT = rabbit

HAM = hamster

HMN = human

MAM = mammal

PGN = pigeon

IVN = intravenous

SCU = subcutaneous

SKN = skin

DRM = dermal

OCC = ocular/corneal

PCP = physico-chemical properties

Legal disclaimer: The above information is believed to be correct but does not purport to be all inclusive and shall be used only as a guide. This company shall not be held liable for any damage resulting from handling or from contact with the above product.