

# AT8033

## Cardioid Condenser Microphone

 audio-technica

broadcast & production microphones



### Features

- **All-purpose condenser microphone ideal for audio acquisition in the studio and on stage; use for interviews, acoustic guitar, percussion, overheads, group vocals and more**
- **Low-mass diaphragm ensures minimum distortion**
- **High SPL capability and wide frequency response**
- **Cardioid polar pattern reduces pickup of sounds from the sides and rear, improving isolation of desired sound source**
- **Switchable 80 Hz high-pass filter minimizes pickup of undesired low-frequency sounds**
- **Offers the convenience of battery or phantom power operation**

### Description

The AT8033 is an all-purpose condenser microphone ideal for general audio acquisition including interviews, acoustic guitar, percussion, overheads, vocals and more.

The microphone requires 11V to 52V phantom power or a 1.5V AA battery for operation. A battery need not be in place for phantom power operation.

The cardioid polar pattern of the microphone is more sensitive to sound originating directly in front of the element, making it useful for controlling feedback and reducing pickup of unwanted sounds.

The output of the microphone is a 3-pin XLRM-type connector.

A switch permits choice of flat response or low-frequency roll-off (via integral 80 Hz high-pass filter) to help control undesired ambient noise.

The microphone is enclosed in a rugged housing. The included AT8405a stand clamp permits mounting on any microphone stand with  $\frac{9}{16}$ "-27 threads. A windscreen, a battery and a soft protective pouch are also included.

### Operation and Maintenance

The AT8033 requires 11V to 52V phantom power or a 1.5V AA battery for operation. A battery need not be in place for phantom power operation.

To install the battery, unscrew the lower section of the microphone body, just below the nameplate. Insert a fresh 1.5V AA battery in the handle compartment ("+" end up), then reassemble the microphone. For longest battery life, the switch should remain off except when the

microphone is in use. Alkaline batteries are recommended for longest life. Remove the battery during long-term storage.

Output is low impedance (Lo-Z) balanced. The signal appears across Pins 2 and 3; Pin 1 is ground (shield). Output phase is "Pin 2 hot"—positive acoustic pressure produces positive voltage at Pin 2.

To avoid phase cancellation and poor sound, all mic cables must be wired consistently: Pin 1-to-Pin 1, etc.

An integral 80 Hz high-pass filter provides easy switching from a flat frequency response to a low-end roll-off. The roll-off position reduces the pickup of low-frequency ambient noise (such as traffic, air-handling systems, etc.), room reverberation and mechanically coupled vibrations. To engage the high-pass filter, slide the switch toward the "bent" line.

The high sensitivity of the microphone assures useful output and an excellent match to most input sources. In some cases, however, an attenuator may be required between the microphone and preamplifier to avoid overloading sensitive input stages.

Avoid leaving the microphone in the open sun or in areas where temperatures exceed 110° F (43° C) for extended periods. Extremely high humidity should also be avoided.

To reduce the environmental impact of a multi-language printed document, product information is available online at [www.audio-technica.com](http://www.audio-technica.com) in a selection of languages.

Afin de réduire l'impact sur l'environnement de l'impression de plusieurs langues, les informations concernant les produits sont disponibles sur le site [www.audio-technica.com](http://www.audio-technica.com) dans une large sélection de langue.

Para reducir el impacto al medioambiente, y reducir la producción de documentos en varios leguajes, información de nuestros productos están disponibles en nuestra página del Internet: [www.audio-technica.com](http://www.audio-technica.com).

Para reduzir o impacto ecológico de um documento impresso de várias linguas, a Audio-Technica providência as informações dos seus produtos em diversas linguas na [www.audio-technica.com](http://www.audio-technica.com).

Per evitare l'impatto ambientale che la stampa di questo documento determinerebbe, le informazioni sui prodotti sono disponibili online in diverse lingue sul sito [www.audio-technica.com](http://www.audio-technica.com).

Der Umwelt zuliebe finden Sie die Produktinformationen in deutscher Sprache und weiteren Sprachen auf unserer Homepage: [www.audio-technica.com](http://www.audio-technica.com).

Om de gevolgen van een gedrukte meertalige handleiding op het milieu te verkleinen, is productinformatie in verschillende talen "on-line" beschikbaar op: [www.audio-technica.com](http://www.audio-technica.com).

本公司基於減少對環境的影響，將不作多語言文件的印刷，有關產品訊息可在 [www.audio-technica.com](http://www.audio-technica.com) 的官方網頁上選擇所屬語言及瀏覽。

本公司基于减少对环境的影响，将不作多语言文档的印刷，有关产品信息可在 [www.audio-technica.com](http://www.audio-technica.com) 的官方网页上选择所属语言和浏览。

자원절약, 환경보호를 위해 국문 사용 설명서는 인쇄하지 않았습니다.  
제품정보는 [www.audio-technica.com](http://www.audio-technica.com) 에서 원하는 언어 선택 후에 다운로드 받으실 수 있습니다.

## Specifications

<b>Element</b>	Fixed-charge back plate, permanently polarized condenser
<b>Polar pattern</b>	Cardioid
<b>Frequency response</b>	30-20,000 Hz
<b>Low frequency roll-off</b>	80 Hz, 18 dB/octave
<b>Open circuit sensitivity</b>	Phantom: -44 dB (6.3 mV) re 1V at 1 Pa Battery: -45 dB (5.6 mV) re 1V at 1 Pa
<b>Impedance</b>	Phantom: 250 ohms Battery: 300 ohms
<b>Maximum input sound level</b>	Phantom: 137 dB SPL, 1 kHz at 1% T.H.D. Battery: 123 dB SPL, 1 kHz at 1% T.H.D.
<b>Dynamic range (typical)</b>	Phantom: 113 dB, 1 kHz at Max SPL Battery: 99 dB, 1 kHz at Max SPL
<b>Signal-to-noise ratio<sup>1</sup></b>	70 dB, 1 kHz at 1 Pa
<b>Phantom power requirements</b>	11-52V DC, 2 mA typical
<b>Battery type</b>	1.5V AA/UM3
<b>Battery current / life</b>	0.4 mA / 1200 hours typical (alkaline)
<b>Switch</b>	Flat, roll-off
<b>Weight</b>	159 g (5.6 oz)
<b>Dimensions</b>	194.2 mm (7.65") long, 26.0 mm (1.02") head diameter
<b>Output connector</b>	Integral 3-pin XLRM-type
<b>Audio-Technica case style</b>	S4
<b>Accessories furnished</b>	AT8405a stand clamp for 5/8"-27 threaded stands; 5/8"-27 to 3/8"-16 threaded adapter; AT8136 windscreen; battery; soft protective pouch

In the interest of standards development, A.T.U.S. offers full details on its test methods to other industry professionals on request.


1 Pascal = 10 dynes/cm<sup>2</sup> = 10 microbars = 94 dB SPL

<sup>1</sup>Typical, A-weighted, using Audio Precision System One.


Specifications are subject to change without notice.



frequency response: 30–20,000 Hz



polar pattern



 **audio-technica**

Audio-Technica Corporation  
[audio-technica.com](http://audio-technica.com) ©2016 Audio-Technica

P51970-01