

ÖLFLEX® HEAT 180 SiHF

Silicone cables with extended temperature range

ÖLFLEX® HEAT 180 SiHF - silicone power and control cable for use in machine and plant construction and toolbuilding for temperatures up to +180°C

Info

The classic for multi-functional use
Further dimensions/colours on request



Temperature-resistant



Halogen-free



Cold-resistant

Benefits

Flexibility simplifies installation where space is limited

Possesses insulating properties after combustion due to remaining SiO₂ ash on the conductor

ÖLFLEX® HEAT 180 SiHF

Application range

Areas with high ambient temperatures where insulating and sheath materials of conventional cables will embrittle after a short while

Typical fields of application

- Steel, ceramic and iron works
- Bakery equipment and industrial furnaces
- Electric motor industry
- Sauna/solarium construction
- Thermal and heating elements
- Lighting technology
- Ventilator engineering
- Air-conditioning technology
- Galvanisation technology

Product features

Halogen-free (IEC 60754-1), no corrosive gases (IEC 60754-2), flame-retardant (IEC 60332-1-2)

Resistant to a multitude of oils, alcohols, vegetable and animal fats and chemical substances

Adequate ventilation must be ensured, since the mechanical properties of silicone cables decrease from +100°C in the absence of air

Norm references / Approvals

Based on EN 50525-2-83

Product Make-up

Fine-wire, tinned-copper conductor

Silicone-based core insulation

Cores twisted in layers

Silicone-based outer sheath,
colour red-brown

Technical Data

Classification ETIM 5:	ETIM 5.0 Class-ID: EC001578 ETIM 5.0 Class-Description: Flexible cable
Classification ETIM 6:	ETIM 6.0 Class-ID: EC001578 ETIM 6.0 Class-Description: Flexible cable
Core identification code:	Colours according to VDE 0293-308, refer to Appendix T9 From 6 cores: black with white numbers
Conductor stranding:	Fine wire according to VDE 0295 Class 5/ IEC 60228 Class 5
Minimum bending radius:	Occasional flexing: 15 x outer diameter Fixed installation: 4 x outer diameter
Nominal voltage:	U0/U: 300/500 V
Test voltage:	2000 V
Protective conductor:	G = with GN-YE protective conductor X = without protective conductor
Temperature range:	-50 °C to +180 °C (adequate ventilation required)

ÖLFLEX® HEAT 180 SiHF

Note

Unless specified otherwise, the shown product values are nominal values. Detailed values (e.g. tolerances) are available upon request.

Copper price basis: EUR 150/100 kg. Refer to catalogue appendix T17 for the definition and calculation of copper-related surcharges.

Please find our standard lengths at: www.lappkabel.de/en/cable-standardlengths

Packaging size: coil \leq 30 kg or \leq 250 m, otherwise drum

Please specify the preferred type of packaging (e.g. 1 x 500 m drum or 5 x 100 m coils).

Photographs and graphics are not to scale and do not represent detailed images of the respective products.

Prices are net prices without VAT and surcharges. Sale to business customers only.

ÖLFLEX® HEAT 180 SiHF

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
ÖLFLEX® HEAT 180 SiHF				
0046001	2 X 0.75	6.4	14.4	59
0046002	3 G 0.75	6.8	21.6	70
00460033	4 G 0.75	7.6	28.8	89
00460043	5 G 0.75	8.5	36	112
0046005	6 G 0.75	9.2	43.2	131
0046006	7 G 0.75	9.2	50.4	136
0046007	2 X 1.0	6.6	19.2	66
0046008	3 G 1.0	7	29	79
00460093	4 G 1.0	7.9	38.4	101
00460103	5 G 1.0	8.8	48	127
0046012	7 G 1.0	9.5	67	156
0046013	2 X 1.5	7.6	29	90
0046014	3 G 1.5	8	43	109
00460153	4 G 1.5	8.8	58	134
00460163	5 G 1.5	9.6	72	163
0046018	7 G 1.5	10.4	101	202
0046039	12 G 1.5	14	173	361
0046040	16 G 1.5	16.2	230.4	478
0046041	20 G 1.5	17.5	288	574
0046042	24 G 1.5	19.8	345.6	720
0046019	2 X 2.5	8.8	48	128
0046020	3 G 2.5	9.7	72	167
00460213	4 G 2.5	10.6	96	206
00460223	5 G 2.5	11.6	120	251
0046024	7 G 2.5	12.6	168	313
0046025	2 X 4.0	10.8	76.8	196
0046026	3 G 4.0	11.5	115	241
00460273	4 G 4.0	12.6	154	300
00460283	5 G 4.0	14	192	374
0046030	7 G 4.0	15.6	269	486
0046031	2 X 6.0	12.4	116	268
0046032	3 G 6.0	13.2	173	333
00460333	4 G 6.0	14.7	230	425

Last Update (03.08.2018)

©2018 Lapp Group - Technical changes reserved

 Product Management www.lappkabel.de

 You can find the current technical data in the corresponding data sheet.
 PN 0456 / 02_03_16

ÖLFLEX® HEAT 180 SiHF

Article number	Number of cores and mm ² per conductor	Outer diameter [mm]	Copper index (kg/km)	Weight (kg/km)
00460343	5 G 6.0	16.6	288	538
0046036	7 G 6.0	18.6	403	705
00460373	4 G 10.0	19.4	384	707
00460453	5 G 10.0	21.6	480	878
00460383	4 G 16.0	21.4	614	1004

Last Update (03.08.2018)

©2018 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03_16