

SPECIFICATIONS

Model No.	F-1000B	F-1000W	F-1000BT	F-1000WT	F-1000BTWP	F-1000WT
Enclosure Type	Bass-reflex type					
Power Handling Capacity	30 W (continuous pink noise) 90 W (continuous program)		—			
Rated Input	—		15 W			
Rated Impedance	8 Ω		100V line: 670Ω (15W), 2 kΩ (5W), 3.3 kΩ (3W), 10 kΩ (1W) 70V line: 330Ω (15W), 670Ω (7.5W), 2 kΩ (2.5W), 3.3 kΩ (1.5W), 10 kΩ (0.5W)			
Sensitivity	87 dB (1W, 1m) at installation in 1/2 free sound field					
Frequency Response	85 - 20,000 Hz, -10 dB at installation in 1/2 free sound field					
Crossover Frequency	5 kHz					
Directivity Angle	Horizontal: 90°, Vertical: 90°					
Speaker Component	Low frequency: 10 cm (4") cone-type High frequency: Balanced dome tweeter					
Input Terminal	Push-in terminal					
Water Protection	—					
Operating Temperature	Equivalent to IPX4 -10°C to +50°C (14°F to 122°F)					
Finish	Enclosure: HIPS, black	Enclosure: HIPS, white	Enclosure: HIPS, black	Enclosure: HIPS, white	Enclosure: HIPS, black	Enclosure: HIPS, white
Dimensions	130 (W) × 202 (H) × 131 (D) mm (5.12" × 7.95" × 5.16")					
Weight	1.8 kg (3.97 lb) (including the supplied brackets)		2 kg (4.41 lb) (including the supplied brackets)			
Accessories	Speaker bracket × 1, Joint bracket × 1, Wall bracket × 1, Bracket fixing screw × 1 set			Speaker bracket × 1, Joint bracket × 1, Wall bracket × 1, Bracket fixing screw × 1 set, Terminal cover × 1, Terminal cover mounting screw × 4		

Model No.	F-1300B	F-1300W	F-1300BT	F-1300WT	F-1300BTWP	F-1300WTWP
Enclosure Type	Bass-reflex type					
Power Handling Capacity	50 W (continuous pink noise) 150 W (continuous program)		—			
Rated Input	—		30 W			
Rated Impedance	8 Ω		100V line: 330Ω (30W), 1 kΩ (10W), 3.3 kΩ (3W), 10 kΩ (1W) 70V line: 170Ω (30W), 330Ω (15W), 1 kΩ (5W), 3.3 kΩ (1.5W), 10 kΩ (0.5W)			
Sensitivity	90 dB (1W, 1m) at installation in 1/2 free sound field					
Frequency Response	80 - 20,000 Hz, -10 dB at installation in 1/2 free sound field					
Crossover Frequency	2 kHz					
Directivity Angle	Horizontal: 110°, Vertical: 100°					
Speaker Component	Low frequency: 13 cm (5") cone-type High frequency: 25 mm (1") dome tweeter					
Input Terminal	Push-in terminal					
Water Protection	—					
Operating Temperature	Equivalent to IPX4 -10°C to +50°C (14°F to 122°F)					
Finish	Enclosure: HIPS, black	Enclosure: HIPS, white	Enclosure: HIPS, black	Enclosure: HIPS, white	Enclosure: HIPS, black	Enclosure: HIPS, white
Dimensions	162 (W) × 250 (H) × 161 (D) mm (6.38" × 9.84" × 6.34")					
Weight	3.1 kg (6.83 lb) (including the supplied brackets)		3.6 kg (7.94 lb) (including the supplied brackets)			
Accessories	Speaker bracket × 1, Joint bracket × 1, Wall bracket × 1, Bracket fixing screw × 1 set			Speaker bracket × 1, Joint bracket × 1, Wall bracket × 1, Bracket fixing screw × 1 set, Terminal cover × 1, Terminal cover mounting screw × 4		

Model No.	F-2000B	F-2000W	F-2000BT	F-2000WT	F-2000BTWP	F-2000WTWP
Enclosure Type	Bass-reflex type					
Power Handling Capacity	60 W (continuous pink noise) 180 W (continuous program)		—			
Rated Input	—		60 W			
Rated Impedance	8 Ω		100V line: 170Ω (60W), 330 Ω (30W), 670 Ω (15W), 3.3 kΩ (3W) 70V line: 83Ω (60W), 170Ω (30W), 330 Ω (15W), 670 Ω (7.5W), 3.3 kΩ (1.5W)			
Sensitivity	92 dB (1W, 1m) at installation in 1/2 free sound field 93 dB (1W, 1m) at installation in 1/2 free sound field (with horn adapter)					
Frequency Response	65 - 20,000 Hz, -10 dB at installation in 1/2 free sound field					
Crossover Frequency	2.5 kHz					
Directivity Angle	Horizontal: 110°, Vertical: 100° Horizontal: 80°, Vertical: 80° (with horn adapter)					
Speaker Component	Low frequency: 20 cm (8") cone-type High frequency: 25 mm (1") dome tweeter					
Input Terminal	Push-in terminal					
Water Protection	—					
Operating Temperature	Equivalent to IPX4 -10°C to +50°C (14°F to 122°F)					
Finish	Enclosure: HIPS, black	Enclosure: HIPS, white	Enclosure: HIPS, black	Enclosure: HIPS, white	Enclosure: HIPS, black	Enclosure: HIPS, white
Dimensions	244 (W) × 373 (H) × 235 (D) mm (9.61" × 14.69" × 9.25")					
Weight	6.5 kg (14.33 lb) (including the supplied brackets)		7.4 kg (16.31 lb) (including the supplied brackets)			
Accessories	Speaker bracket × 1, Joint bracket × 1, Wall bracket × 1, Bracket fixing screw × 1 set, Horn adapter × 1, Horn adapter mounting screw × 4			Speaker bracket × 1, Joint bracket × 1, Wall bracket × 1, Bracket fixing screw × 1 set, Horn adapter × 1, Horn adapter mounting screw × 4, Terminal cover × 1, Terminal cover mounting screw × 4		



F SERIES WIDE-DISPERSION SPEAKER SYSTEM



*Compact and versatile
sound reinforcement solutions*



Human Society with
Sound & Communication

TOA Corporation
www.toa.co.uk

Specifications are subject to change without notice.

Compact high performance and unmatched installation versatility.



F-2000

F-1300

F-1000

Innovative octagonal horn provides wide dispersion


Significantly improved 110° × 100° high-frequency dispersion angle, for better sound coverage and a more even tonal balance.

F-2000: 110° × 100°



F-1300: 110° × 100°

F-1000: 90° × 90°

Easily mountable adapter included (F-2000 only), for applications requiring more controlled dispersion.



•HF Horn Adapter for F-2000



The latest addition to TOA's acclaimed speaker line, the new F Series of compact, high efficiency two-way speakers achieve higher performance levels for wide range frequency response and power handling. Designed to be extremely versatile in order to meet different installation and application requirements, the new F Series are ideal solutions that solve increasing needs for adaptable sound reinforcement.




Various mount brackets

Accessory brackets enable a wide variety of installations, for example on walls, ceilings and speaker stands. Moreover, additional available brackets make even more demanding installations possible.




Stylish and highly rigid speaker casing design

The F Series speaker casing comes with a design that is highly stylish, so it blends well into a room's decor and can be attractively installed. The graceful, lightly convex bulge on the side of the casing is also part of a rigidity-enhancing casing construction that works for clear sound reproduction.


Accessory brackets enable:



Optional Accessories



Recommended Optional Subwoofers




For any environment

The F Series also features a waterproof design. The speakers may also be re-painted as desired.



Built-in speaker protection



Impedance matching

for optimal amplifier/speaker performance.



Easy connecting

Push-in terminals allow quick connections.

