

# 97 78 180 T

## Crimping Pliers for end sleeves (ferrules) with tether attachment point



- For crimping end sleeves (ferrules) according to DIN 46228 parts 1 + 4 from 0.25 to 16 mm<sup>2</sup>
- Improved leverage for 30% easier crimping
- Light and slim design
- Crimping in marked half-round dies for reliable connections between the sleeve and the conductor
- 9 particularly deep dies with conical side faces
- Special tool steel, forged, oil-hardened
- Pliers with integrated, insulated tether attachment point for a tool tether



<b>Article No.</b>	97 78 180 T
<b>EAN</b>	4003773081531
<b>Head</b>	polished
<b>Handles</b>	insulated with multi-component grips, VDE-tested with integrated insulated tether attachment point for a tool tether
<b>Insulation standard</b>	IEC 60900 DIN EN 60900
<b>Capacity in square millimetres mm<sup>2</sup></b>	0,25 - 16,0
<b>Applications</b>	End Sleeves (ferrules)
<b>Number of crimping positions</b>	9
<b>AWG</b>	23 - 5
<b>Length mm</b>	180
<b>Net weight g</b>	254



technical change and errors excepted