

Accessories
TS 35X7.5 2M/ST/ZN

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com

**Building installation wiring**

For building installations, we offer a complete system that revolves around the 10×3 copper rail and comprises perfectly coordinated components: from installation terminal blocks, neutral conductor terminal blocks and distribution terminal blocks to comprehensive accessories such as busbars and busbar holders.

General ordering data

| | |
|------------|---|
| Type | TS 35X7.5 2M/ST/ZN |
| Order No. | 0383400000 |
| Version | Mounting rail, TS 35, TS 35 x 7.5, without slot, Steel, galvanized, chromium-plated |
| GTIN (EAN) | 4008190088026 |
| Qty. | 2 m |

Data sheet

Accessories TS 35X7.5 2M/ST/ZN

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com

Technical data

Dimensions and weights

| | | | |
|------------|--------|-----------------|------------|
| Width | 35 mm | Width (inches) | 1.378 inch |
| Height | 35 mm | Height (inches) | 1.378 inch |
| Depth | 7.5 mm | Depth (inches) | 0.295 inch |
| Net weight | 325 g | | |

Material data

| | | | |
|----------|--------|----------------|-----------------------------|
| Material | Steel | Surface finish | galvanized, chromium-plated |
| Colour | Silver | | |

System specifications

| | | | |
|---------|--------------|---------------|--------------------|
| Version | without slot | Mounting rail | TS 35, TS 35 x 7.5 |
|---------|--------------|---------------|--------------------|

Additional technical data

| | | | |
|---------------------|-----------------|------------------|---------|
| Installation advice | Direct mounting | Type of mounting | Screwed |
|---------------------|-----------------|------------------|---------|

Mounting rail

| | | | |
|---|--------------------|-----------|------|
| Short circuit strength corresponds to E-Cu wire | 16 mm ² | Thickness | 1 mm |
|---|--------------------|-----------|------|

Rating data

| | |
|-----------|--------------|
| Standards | DIN EN 60715 |
|-----------|--------------|

Classifications

| | | | |
|------------|-------------|------------|-------------|
| ETIM 3.0 | EC001285 | ETIM 4.0 | EC001285 |
| ETIM 5.0 | EC001285 | ETIM 6.0 | EC001285 |
| UNSPSC | 30-21-18-01 | eClass 5.1 | 27-14-06-04 |
| eClass 6.2 | 27-14-11-43 | eClass 7.1 | 27-14-11-43 |
| eClass 8.1 | 27-14-11-43 | eClass 9.0 | 27-14-11-43 |
| eClass 9.1 | 27-40-06-02 | | |

Product information

| | |
|--------------------------------|---|
| Descriptive text ordering data | TS 35X7.5 2M/AL/BK: max. permitted rated current for PEN function = 125 A |
|--------------------------------|---|

Approvals

| | |
|------|---------|
| ROHS | Conform |
|------|---------|

Downloads

| | |
|--------------------|--|
| Brochure/Catalogue | CAT 1 TERM 16/17 EN |
| Engineering Data | EPLAN, WSCAD, Zuken E3.S |
| Engineering Data | STEP |