

Description

Builder Black PSUs are certified RoHS compliant and with power factor control-giving you a safe and stable foundation to build your system from. They come with a sleeve bearing 12cm fan that offers a quiet operation but with excellent cooling meaning you are working in a more peaceful environment and the right cooling ensures maximum lifespan of your products. Supplied with all the appropriate cables including 3 SATA providing maximum compatibility with popular CPU's and mainboards.

Key Features

- **Support** - Compliant with latest Intel standards ATX 12V, V2.0
- **Efficiency** > 70%
- **MTBF** > 50000hrs
- **Cooling System** - 120mm sleeve bearing fan
- **Protection** - Over Voltage Protection (OVP), Under Voltage, Over Power Protection (OPP), Over Temperature Protection (OTP) & Short Circuit Protection (SCP)

PSU Specifications

AC INPUT: 230 VAC 5A 50-60Hz					
DC	+3.3V	+5V	+12V1	-12V	+5VSB
Output	26A	27A	22A	0.5A	2A
Max	500W				

Connectors



20+4 Pin Main Connectors:

1




4-Pin 12V Connectors:

1




SATA Connectors:

3



4-Pin Molex Connectors:

2



Floppy Drive Connectors:

1

Detailed Specifications

Dimensions: 150mm x 86mm x 142mm (W x H x D)

Input Voltage: 230 VAC

Input Current: 5A

Input Frequency Range: 50-60Hz

PFC: Passive PFC

Power Good: 100-500 ms

Signal:
Hold Up Time: >17ms
Efficiency: >70%
MTBF: 50,000 Hours
Protection: OVP / OTP / OCP/ OLP/ OPP/ SCP
Power: 500W
Operation Temperature: 0-40°C (Nominal Input Voltage)
Safety: CE / FCC / UL / TUV
Cooling: 12cm Fan
Noise: < 23 dBA

General Specifications

Manufacturer: 500W BUILDER BLACK
Part Number:
EAN Number: 5055492430878
Has Mains Plug: No
Colour: Black
What's In The Box: PSU
Unit (Product) Dimensions (mm): 150mm x 86mm x 142mm (W x H x D)
Packaging Dimensions (mm): 203mm x 162mm x 92mm (W x H x D)
Net Weight (KGs): 1.1 KGs
Gross Weight (KGs): 1.2 KGs