

SAIB-M23-19P-AN-5,0M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16


D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com



Sensor/actuator cables are used for wiring sensors and actuators and for transmitting data or power in various applications. The moulded cable offers connected and tested connection of the plug-in connector to the cable ex-works. The cables may be exposed to a wide range of conditions, such as humidity, dust, heat, cold, shock or vibration.

The M23 cables offer: high mating frequency, high current carrying capacity and high-density contacts coupled with minimal dimensions.

Is there something you have not managed to find or you feel needs explanation? Talk to us!

General ordering data

Type	SAIB-M23-19P-AN-5,0M
Order No.	1818140500
Version	Sensor/actuator line, One end without connector, M23, No. of poles: 19, 5 m, Socket, angled, Shielded: No, LED: No, Sheath material: PUR, Halogen: No
GTIN (EAN)	4032248473915
Qty.	1 pc(s).

SAIB-M23-19P-AN-5,0M

Weidmüller Interface GmbH & Co. KG

Klingenbergstraße 16

D-32758 Detmold

Germany

Fon: +49 5231 14-0

Fax: +49 5231 14-292083

www.weidmueller.com

Technical data

Dimensions and weights

Net weight	704 g
------------	-------

Temperatures

Operating temperature range, max.	125 °C	Operating temperature range, min.	-40 °C
Operating temperature, max.	125 °C	Operating temperature, min.	-40 °C

Technical specifications for cable

Number of poles	19	Wire cross section	12-pole (8x0.34+3x0.75)/19-pole (16x0.34+3x0.75)
Outside diameter	9.1 ± 0.3 mm	Shielded	No
Insulation	TPM	Colour coding	violet, red, grey, red / blue, green, blue, grey / pink, white / green, white / yellow, white / grey, black, green / yellow, Yellow / brown, brown / green, white, yellow, pink, grey / brown, brown
Sheath material	PUR	Sheathing colour	Black
Cable length	5 m	Temperature range, moving	-5...80 °C
Temperature range, stationary	-40...80 °C	Halogen	No
Suitable for cable carriers	Yes	Torsion resistance	0 °/m
Bending radius, min., moving	10 x cable diameter	Bending cycles	2 Mio
Resistant to welding beads	No		

General technical data

Version	Socket, angled	connection thread	M23
Housing main material	PUR	Threaded ring material	Diecast zinc
Protection degree	IP67	Contact surface	Gold-plated
LED	No	Rated voltage	150 V
Rated current	8 A	Insulation resistance	10 ¹² Ω
Temperature range of housing	-40...+125 °C	Tightening torque	M23: 2.5 Nm
Pollution severity	2	jumpered	No

Classifications

ETIM 3.0	EC001855	ETIM 4.0	EC001855
ETIM 5.0	EC001855	ETIM 6.0	EC001855
UNSPSC	26-12-16-13	eClass 5.1	27-06-91-90
eClass 6.2	27-06-91-90	eClass 7.1	27-06-91-90
eClass 8.1	27-06-91-90	eClass 9.0	27-06-91-90
eClass 9.1	27-06-03-11		

Product information

Descriptive text ordering data	Other versions on request
Descriptive text technical data	Chapter W includes additional technical specifications for the cable

SAIB-M23-19P-AN-5,0M**Weidmüller Interface GmbH & Co. KG**
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-292083
www.weidmueller.com**Technical data****Approvals**

Approvals



ROHS

Conform

Downloads

Brochure/Catalogue

[FL FIELDWIRING EN](#)

Engineering Data


[EPLAN, WSCAD](#)

SAIB-M23-19P-AN-5,0M

Weidmüller Interface GmbH & Co. KG
 Klingenbergstraße 16
 D-32758 Detmold
 Germany
 Fon: +49 5231 14-0
 Fax: +49 5231 14-292083
 www.weidmueller.com


Drawings

Dimensioned drawing




Angled socket

Pole scheme



Socket

Wiring diagram



The ideal tool, the Screwty® with torque function



Light, securely screwed-in round plug-in connectors. Screwty set DM / VPE: 1 / Order No.: 1920000000 Adapters: M12, M12 F, M8, M8 F