

Part Number: [0039014036](#)
 Status: Active
 Overview: [Mini-Fit Jr. Power Connectors](#)
 Description: Mini-Fit Jr. Plug Housing, Single Row, 3 Circuits, UL 94V-2, without Panel Mounting Ears, Natural

Documents:

3D 모델	제품규격 TS-5556-002-001 (PDF)
도면 (PDF)	Application Specification AS-5557-001-001 (PDF)
제품규격 PS-45750-001-001 (PDF)	Packaging Specification PK-5559-003-001 (PDF)
제품규격 PS-5556-001-001 (PDF)	RoHS 증명서(PDF)

Agency Certification

CSA	LR19980
UL	E29179

일반적 특성

적용제품 설명
 Power, 와이어 대 보드, 와이어 대 와이어
 Current = 13A max. per circuit when header is mated to a receptacle loaded with [45750](#) series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.

전체보기

제품명 [Mini-Fit Jr. Power Connectors](#)
 UPC Mini-Fit Jr. 800754381109

물리적 특성

분리형	No
최대 회로수	3
색상 - Resin	Natural
난연성	94V-2
암수구분	플러그
Glow-Wire Capable	No
Keying to Mating Part	없음
결합제품 잠금장치	Yes
원재료 - 플라스틱	나일론 (PA)
Net Weight	1.160/g
열 수	1
포장타입	백 (Bag)
패널마운트	No
피치 - 결합부	4.20mm
피치 - 터미널 간격	4.20mm
결합제품 오삽입 장치	Yes
End-to-End 연결형	No
사용온도 범위	-40° to +105°C

전기적 특성

전류 - 접촉 당 최대 출력 13.0A

납땜 프로세스 정보


Lead-free Process Capability N/A

원재료 정보

Engineering Number 5559-03P3

참고 - 도면번호

Application Specification AS-5557-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series
[5559](#) Series

Mates With
Receptacle Housing [39-01-4030](#)

Use With
[5558](#) Mini-Fit Jr. Male Crimp Terminals.
[30490](#) Mini-Fit Male Grounding Crimp Terminals
 [46012](#) Mini-Fit Plus Crimp Terminal

Packaging Specification
제품규격
도면

PK-5559-003-001
PS-45750-001-001, PS-5556-001-001, TS-5556-002-001
55590300-SD-000

This document was generated on 09/20/2018
PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION