

## SECTION 1: Identification of the substance/mixture and of the company/undertaking

- 1.1 Product identifier** O'Keeffe's Working Hands Cream Jar
- 1.2 Relevant identified uses of the substance/mixture and uses advised against**  
Hand Cream – skincare product
- 1.3 Details of the Supplier of the Safety Data Sheet**  
Gorilla Glue Europe Ltd.  
Chorley Business & Technology Centre  
East Terrace, Euxton Lane,  
Chorley, Lancashire  
PR7 6TE  
eusales@gorillaglu.com
- 1.4 Emergency telephone number**  
+44 0843 507 1200

## SECTION 2: Hazards identification

- 2.1 Classification of the substance or mixture**  
This product is classified as not hazardous in accordance with Regulation (EC) No 1272/2008 (CLP).
- 2.2 Label elements**
- |                           |                  |                     |                            |
|---------------------------|------------------|---------------------|----------------------------|
| <b>Health Hazards</b>     | None Classified. | <b>GHS Labeling</b> | Hazardous Symbols: None    |
| <b>Physical Hazards</b>   | None Classified  |                     | Signal Word: None          |
| <b>Hazard Category</b>    | None Classified. |                     | Hazardous Statements: None |
| <b>Routes of Exposure</b> | None Classified. |                     | Precautionary Statements   |
|                           |                  |                     | Prevention: None           |
|                           |                  |                     | Response: None             |
|                           |                  |                     | Storage: None              |
|                           |                  |                     | Disposal: None             |
- 2.3 Other hazards**  
None if used properly.

## SECTION 3: Composition / information on ingredients

Hazardous components

Chemical Name	Concentration %
Sodium Hydroxide	*

\*concentration is proprietary

---

## SECTION 4: First aid measures

---

### 4.1 Description of first aid measures

#### Eyes

Immediately flood the eye with plenty of water for at least 15 minutes, holding the eye open. Obtain medical attention if soreness or redness persists.

#### Skin

None

#### Ingestion

Rinse mouth out and drink plenty of water.

#### Inhalation

Under normal conditions of use, no expected risks are posed by inhalation. If irritation occurs, seek fresh air.

#### Advice to Physicians

Treat symptomatically.

### 4.2 Most important symptoms and effects, both acute and delayed

Skin: Mild stinging sensation may occur.

### 4.3 Indication of any immediate medical attention and special treatment needed

See Section 4.1 Description of first aid measures.

---

## SECTION 5: Firefighting measures

---

### 5.1 Extinguishing Media

#### Suitable extinguishing media:

Not Flammable - Use any extinguishing media that is suitable for the surrounding fire.

#### Extinguishing media which must not be used for safety reasons:

None – Use any extinguishing media that is suitable for the surrounding fire.

### 5.2 Special hazards arising from the substance or mixture

None.

### 5.3 Advice for firefighters

Please wear the appropriate protective clothing and/or breathing apparatus that is suitable for the surrounding fire.

---

## SECTION 6: Accidental release measures

---

### 6.1 Personal precautions, protective equipment, and emergency procedures

No special measures are required.

### 6.2 Environmental precautions

No special measures are required.

### 6.3 Methods and materials for containment and cleaning up

Scoop up and transfer material into a suitable container for recovery or disposal. Wash spilled area thoroughly with soap and water.

## 6.4 Reference to other sections

Please see Section 8.

## SECTION 7: Handling and storage

### 7.1 Precaution for safe handling

None necessary.

### 7.2 Conditions for safe storage, including any incompatibilities

Store at room temperature.

### 7.3 Specific end use(s)

Hand Cream

## SECTION 8: Exposure controls / personal protection

### 8.1 Control parameters

Sodium Hydroxide		
Austria	MAK	2 mg/m <sup>3</sup>
Austria	KZW	4 mg/m <sup>3</sup>
Belgium	TWA	2 mg/m <sup>3</sup>
Denmark	CL	2 mg/m <sup>3</sup>
Finland	CL	2 mg/m <sup>3</sup>
France	VME	2 mg/m <sup>3</sup>
Hungary	TWA	2 mg/m <sup>3</sup>
Iceland	STEL	2 mg/m <sup>3</sup>
Netherlands	MAC-TGG	2 mg/m <sup>3</sup>
Norway	TWA	2 mg/m <sup>3</sup>
Poland	MAC (TWA)	0,5 mg/m <sup>3</sup>
Poland	MAC (STEL)	1 mg/m <sup>3</sup>
Sweden	TWA	1 mg/m <sup>3</sup>
Sweden	CL	2 mg/m <sup>3</sup> (inhalable dust)
Switzerland	CL	2 mg/m <sup>3</sup> (inhal)
Turkey	TWA	2 mg/m <sup>3</sup>
United Kingdom	STEL	2 mg/m <sup>3</sup>

### 8.2 Exposure controls

#### Engineering control

No specific measures necessary.

#### Personal Protective Measures

##### Respiratory/Skin/Eye/Face/Body Protection

Not required when used under normal conditions.

## SECTION 9: Physical and chemical properties

### 9.1 Information on basic physical and chemical properties

<b>Physical State</b>	Solid: cream	<b>pH</b>	6.0 – 7.8
<b>Color</b>	White	<b>Density (g/l, g/yd<sup>2</sup>)</b>	Not applicable
<b>Odor</b>	Mild Stearic Acid odor	<b>Specific Gravity</b>	1.03 – 1.06 g/ml
<b>Odor Threshold</b>	No data available	<b>Melting Point (°C/F)</b>	Not applicable
<b>Boiling Range/Point (°C/F)</b>	> 100°C	<b>Vapor Pressure</b>	Not applicable
<b>Flash Point (PMCC) (°C/F)</b>	None	<b>Solubility in Water</b>	Not Miscible
<b>Evaporation Rate (BuAc=1)</b>	Not applicable	<b>Viscosity</b>	Not applicable
<b>Vapor Density (Air = 1)</b>	Not applicable	<b>Auto-Ignition Temperature</b>	Not applicable
<b>VOC (g/l)</b>	Not applicable	<b>Decomposition Temperature</b>	Not applicable
<b>VOC (%)</b>	Not applicable	<b>Upper Explosive Limit</b>	Not applicable
<b>Partition Coefficient</b> (n-octanol/water)	Not applicable	<b>Lower Explosive Limit</b>	Not applicable
<b>Flammability (solid / gas)</b>	Not applicable		

### 9.2 Other information

No data available.

## SECTION 10: Stability and reactivity

### 10.1 Reactivity

Data is not available.

### 10.2 Chemical stability

Stable under normal conditions.

### 10.3 Possibility of hazardous reactions

None.

### 10.4 Conditions to avoid

None.

### 10.5 Incompatible materials

None.

### 10.6 Hazardous decomposition products

None.

## SECTION 11: Toxicological information

### 11.1 Information on toxicological effects

#### Acute toxicity

No relevant studies identified.

#### Specific target organ systemic toxicity (STOT single and repeat)

No relevant studies identified.

#### Serious eye damage / eye irritation

No relevant studies identified.

#### Skin corrosion / irritation

Not a skin irritant (HRIPT, 2015)

#### Respiratory sensitization

No data is available to indicate this product may be a respiratory sensitizer.



### **Skin sensitization**

Not a skin sensitizer (HRIPT, 2015)

### **Carcinogenicity**

No relevant studies identified.

### **Germ cell mutagenicity**

No relevant studies identified.

### **Aspiration hazard**

No relevant studies identified.

---

## **SECTION 12: Ecological information**

---

### **12.1 Toxicity / 12.2 Persistence and degradability / 12.3 Bioaccumulative potential / 12.4 Mobility in soil / 12.5 Results of PBT and vPvB assessment / 12.6 Other adverse effects**

No data available.

---

## **SECTION 13: Disposal considerations**

---

### **13.1 Waste treatment methods**

Dispose of in accordance with all applicable local, state, federal, and national regulations.

---

## **SECTION 14: Transport information**

---

### **14.1 UN number / 14.2 UN proper shipping name / 14.3 Transport hazard class(es) / 14.4 Packaging group**

Not dangerous goods.

### **14.5 Environmental hazards / 14.6 Special precautions for user 14.7 Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code**

Not applicable.

---

## **SECTION 15: Regulatory information**

---

### **15.1 Safety, health and environmental regulations / legislation specific for the substance or mixture**

No information is available.

### **15.2 Chemical safety assessment**

A chemical safety assessment has not been carried out.

---

## **SECTION 16: Other information**

---

The information presented in this Safety Data Sheet was prepared by qualified personnel and to the best of our knowledge is true and accurate. The information and recommendations are furnished for this product with the understanding that the purchaser will independently determine the suitability of the product for this purpose. This data does not constitute a warranty, expressed or implied, statutory or otherwise, nor is it representation for which the O'Keeffe's Company assumes legal responsibility. The data is submitted for the user's information and consideration only. Any use or disposal of this product must be determined by the user to be in with applicable national, federal, state, provincial and local laws and regulations.