


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5013340000](#)
Status: **Active**
Overview: Pico-Clasp Wire-to-Board Connectors
Description: Pico-Clasp 1.00mm Pitch Wire-to-Board Crimp Terminal, 28-32 AWG, Tin Plating, Reel

Documents:

3D Model	Product Specification PS-501940-001-001 (PDF)
Drawing (PDF)	Packaging Specification SPK-501334-001-001 (PDF)
Product Specification PS-501331-001-001 (PDF)	RoHS Certificate of Compliance (PDF)



General

Product Family	Crimp Terminals
Series	501334
Application	Signal, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	Pico-Clasp Wire-to-Board Connectors
Packaging Alternative	501334-0100 (Loose)
Product Name	Pico-Clasp
UPC	822348531103

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	8.600/mg
Packaging Type	Reel
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.80mm max.
Wire Size AWG	28, 30, 32
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	1.0A
-------------------------------	------

Material Info

Reference - Drawing Numbers

Crimp Specification	CS-501193-001-001
Packaging Specification	SPK-501334-001-001
Product Specification	PS-501331-001-001, PS-501940-001-001
Sales Drawing	5013340000-SD-000

EU ELV

Compliant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/61/2018 (27 June
2018)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Compliant
Prop65	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[501334](#) Series

Mates With

[501331](#) PCB Header for Pico-Clasp .
[104051](#) PCB Header for IllumiMate

Use With

[501330](#) Crimp Housing for Pico-Clasp .
[104050](#) Crimp Housing for IllumiMate