

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0528081470

Status:

Active

Overview:

FFC-FPC (SMT)

Description:

1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, 14 Circuits



Documents:

[3D Model](#)

[Drawing \(PDF\)](#)

[Product Specification PS-52808-004-001 \(PDF\)](#)

[Packaging Specification 528089200-200 \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E29179
General	
Product Family	FFC/FPC Connectors
Series	52808
Overview	FFC-FPC (SMT)
Product Name	Easy-On
UPC	822348142798
Physical	
Actuator Type	Non-ZIF
Circuits (Loaded)	14
Circuits (maximum)	14
Color - Resin	Natural
Contact Position	N/A
Durability (mating cycles max)	10
Mated Height	5.05mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	High Temperature Thermoplastic
Net Weight	378.400/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	125V AC (RMS)/DC
Material Info	
Reference - Drawing Numbers	
Packaging Specification	528089200-200
Product Specification	PS-52808-004-001
Sales Drawing	SD-52808-027, SD-52808-028

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per - ED/61/2018 (27 June 2018)

Halogen-Free Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Green Image

ELV

Not Relevant

Prop65

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

52808 Series

This document was generated on 09/11/2018

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION