



PSG3033 DIGITAL TO ANALOG AUDIO CONVERTER

IMPORTANT SAFETY INFORMATION

Please read these instructions carefully before use and retain for future reference.

 Check that the voltage indicated on the PSU rating plate corresponds with that of the local network before connecting to the mains power supply.

OVERVIEW

 This device converts Coaxial or Toslink digital audio signals to analogue L/R audio for connection to an external device such as an amplifier via standard RCA style jacks.

WHAT'S IN THE BOX

- · Main unit.
- · 5V DC Power Supply.
- User's Manual.

INSTALL ATION

- Please make sure all devices you wish to connect have been powered off.
- Connect the audio source device to the converter using appropriate Coaxial or Toslink cable.
- · Connect the output RCA jacks to the AV receiver or amplifier using phono cables.
- · Do not connect the audio cables with the unit powered on.
- Connect the DC side of 5V power supply to the converter and then connect the AC side of the power supply into the mains supply.
- The power LED lights when the power is applied.

SPECIFICATIONS

Operating environment	0-40° / Storage -10 to 55°, Humidity up to 90%
Power supply	220-240V~50Hz
Power requirement	5V DC 1A
Power consumption (max)	3W
Input	Support 24-bit S/PDIF Toslink or Coaxial
Audio sampling rate	32KHz, 44.1KHz, 48KHz, 96KHz
Output	RCA Phono LR
Dimensions	65.5 x 41 x 26.5mm
Weight (not inc PSU)	70g



INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.

Made in China. PR2 9PP Man Rev 1.0