

Features & Benefits:

- Snap-Locking Sprung Hook
- Easily replaceable tip
- Large accessory set
- Meets IEC 61010-031
- RoHS compliant

Accessories included: 15 cm Ground Lead, Replacement Tip, Black Snap-on Sprung Hook, Tip Insulator, IC Tip, BNC Adapter, Probe Tip Ground, Trimmer Tool & Identifier Rings.

The High Performance family is a high quality, general purpose set of 5mm Passive Voltage Oscilloscope probes. They are excellent replacement probes for all makes and models of oscilloscopes.

SPECIFICATIONS:

Type	5 mm Passive Voltage
Bandwidth	15/100 MHz
Attenuation	1x/10x
Input Impedance	1/10 M Ω
Input Capacitance	45/16 pF
Output Impedance	1 M Ω
Risetime	27/3.5 ns
IEC Rating	300 V CAT II
Compensation	10–35 pF
Cable Length	1.2 m
Readout Actuator	–
Operating Temperature	0° to +50° C
Humidity	85% RH or less (at 35° C)
RoHS (2011/65/EU)	Compliant