



ESD SAFE

BRIGHT LEDs

DIMMABLE

MODERN & ERGONOMIC
DESIGN

Omega 5 ESD

MAGNIFYING LAMP

Our Omega 5 ESD Magnifier uses carbon-fibre and special conductive coatings to guarantee 100% ESD compliance for the lifetime of the magnifier. The 12.7cm (5") diameter, 3 diopter (1.75X) glass lens provides the largest field of view to allow precise inspection. An optional 12.7cm (5") diameter, 5 diopter (2.25X) lens is available separately.

5
great
reasons to use
Daylight
magnifiers



CONTRAST



BRIGHTER



SPREAD
OF LIGHT



ERGONOMICS



HEALTHY
VISION



MAGNIFICATION

+44 (0)20 8964 1200

www.daylightcompany.com



D/E25151

Omega 5 ESD Magnifier

- ★ Ergonomic and professional ESD safe magnifying lamp
- ★ 42 daylight premium LEDs with 2 brightness levels
- ★ 12.7cm (5") 3D (1.75X) glass lens with anti-static coating included
- ★ Suitable for use in EPA, (Electrostatic Protected Areas) To IEC 61340-5-1 and ANSI/ESD 20:20
- ★ Unique quick change lens mechanism - no tools required
- ★ Heavy duty arm with reinforced joints



Available Accessories



5 Diopter ESD Glass
Lens
D65151

Product Information

Width	18cm (7.1")
Height	58.5cm (23")
Depth	78cm (30.7")
Weight	2.4kg (5.2lb)
Colour	Black
Reach	115.1cm (45.3")
Cable Length	2.6m (102.4")
Lens Size	12.7cm (5")
Magnification	3D (1.75X)
Extra Magnification available separately	5D (2.25X) (D65151)
Lens Material	Optical Quality Glass

Light Output

Light Source	LED
Lumens	548lm
Lux	5,500 Lux at 15cm (6")
Colour Temperature	6,000°K
Power Consumption	8W

Packaging Information

Width	54cm (21.3")
Height	42cm (16.5")
Depth	10cm (3.9")
Packed Weight per unit	3.3kg (7.2lb)
Products per Master Carton	2

+44 (0)20 8964 1200
www.daylightcompany.com

