



MPA-202

Order No.: 32.0710

Price upon request

PRODUCTINFOS

2-channel low-noise microphone preamplifier

- 2 microphone inputs, XLR, bal.
- Gain control, 11 steps, 20-70 dB
- 2 level controls ± 5 dB
- LED green/red for indicating operation/peak
- Phantom power +12 V, can be activated as required
- Microphone phase, switchable for each channel
- Low cut: 15-240 Hz, continuously adjustable
- Subsonic filter 15 Hz, 18 dB/oct.
- 2 line outputs, XLR bal.
- 2 line outputs, RCA unbal.

TECHNICAL SPECIFICATIONS

MPA-202

Type microphone preamplifier

MPA-202

Frequency range	20-20,000 Hz
Input sensitivity	0.16-150 mV schaltbar 4.4 k Ω (bal.)
Input impedance	2.2 k Ω (unbal.)
Output signal	1-14 V (line, bal.) 1-7 V (line, stereo)
Output impedance	100 Ω /600 Ω
Gain	15-75 dB
Crossover frequency	15-240 Hz, 6 dB/oct. (low cut), 15 Hz, 18 dB/oct. (subsonic)
Low cut	15-240 Hz, 6 dB/oct.
S/N ratio	> 68 dB, unweighted > 87 dB, weighted
THD	< 0,01%
Admiss. ambient temp.	0-40 °C
Power supply	via encl. plug-in power supply
Dimensions	116 x 55 x 135 mm
Weight	980 g
Inputs	2 x XLR 2 x XLR
Outputs	2 x RCA