



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 11

TEROSON MS 930 WH

SDS No. : 266857  
V003.0

Revision: 31.01.2018

printing date: 24.08.2018

Replaces version from: 26.02.2015

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

TEROSON MS 930 WH

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:

Sealant

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd

Wood Lane End

HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 0 8701 906777 - For further general health & safety, technical and practical advice on this product, please call +44 (0) 1606 593933 or write to: Technical Services; Henkel Limited; Road 5; Winsford Industrial Estate; Winsford; Cheshire; CW7 3QY- Email: technical.services@henkel.co.uk

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

#### 2.2. Label elements

##### Label elements (CLP):

The substance or mixture is not hazardous according to Regulation (EC) No 1272/2008 (CLP).

##### Supplemental information

**EUH210 Safety data sheet available on request.**

Contains Dibutoxydibutylstannane. May produce an allergic reaction.

#### 2.3. Other hazards

None if used properly.

Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

##### General chemical description:

Sealant

##### Base substances of preparation:

Silane-modified polyether

##### Declaration of the ingredients according to CLP (EC) No 1272/2008:

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Dibutoxydibutylstannane 3349-36-8	222-103-1 01-2119557858-18	0,1- < 1 %	Skin Corr. 1C; Dermal H314 Skin Sens. 1 H317 Muta. 2 H341 Repr. 1B H360FD STOT SE 1 H370 STOT RE 1 H372 Aquatic Chronic 2 H411

For full text of the H - statements and other abbreviations see section 16 "Other information".  
Substances without classification may have community workplace exposure limits available.

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

##### Inhalation:

Move to fresh air, consult doctor if complaint persists.

##### Skin contact:

Rinse with running water and soap. Apply replenishing cream. Change all contaminated clothing. If necessary, see a dermatologist.

##### Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

##### Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

#### 4.2. Most important symptoms and effects, both acute and delayed

An allergic reaction cannot be excluded after repeated skin contact.

#### 4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

##### Suitable extinguishing media:

All common extinguishing agents are suitable.

##### Extinguishing media which must not be used for safety reasons:

High pressure waterjet

**5.2. Special hazards arising from the substance or mixture**

In case of fire toxic gases can be released.

**5.3. Advice for firefighters**

Wear self-contained breathing apparatus.

Wear protective equipment.

**SECTION 6: Accidental release measures****6.1. Personal precautions, protective equipment and emergency procedures**

Wear protective equipment.

**6.2. Environmental precautions**

Do not empty into drains / surface water / ground water.

**6.3. Methods and material for containment and cleaning up**

Remove mechanically.

Dispose of contaminated material as waste according to Section 13.

**6.4. Reference to other sections**

See advice in section 8

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

Hygiene measures:

Do not eat, drink or smoke while working.

Wash hands before work breaks and after finishing work.

**7.2. Conditions for safe storage, including any incompatibilities**

Ensure good ventilation/extraction.

Store in a cool, frost-free place.

Storage at 15 to 25°C is recommended.

**7.3. Specific end use(s)**

Sealant

## SECTION 8: Exposure controls/personal protection

### 8.1. Control parameters

#### Occupational Exposure Limits

Valid for  
Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, INHALABLE DUST]		10	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [LIMESTONE, RESPIRABLE MARBLE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Calcium carbonate 471-34-1 [LIMESTONE, TOTAL INHALABLE MARBLE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL
Di-"isononyl" phthalate 28553-12-0 [DIISONONYL PHTHALATE]		5	Time Weighted Average (TWA):		EH40 WEL
Titanium dioxide 13463-67-7 [TITANIUM DIOXIDE, TOTAL INHALABLE]		10	Time Weighted Average (TWA):		EH40 WEL
Titanium dioxide 13463-67-7 [TITANIUM DIOXIDE, RESPIRABLE]		4	Time Weighted Average (TWA):		EH40 WEL
Dibutoxydibutylstannane 3349-36-8 [TIN COMPOUNDS, ORGANIC, EXCEPT CYHEXATIN (ISO), (AS SN)]		0,1	Time Weighted Average (TWA):		EH40 WEL
Dibutoxydibutylstannane 3349-36-8 [TIN COMPOUNDS, ORGANIC, EXCEPT CYHEXATIN (ISO), (AS SN)]		0,2	Short Term Exposure Limit (STEL):		EH40 WEL
Dibutoxydibutylstannane 3349-36-8 [TIN COMPOUNDS, ORGANIC, EXCEPT CYHEXATIN (ISO), (AS SN)]			Skin designation:	Can be absorbed through the skin.	EH40 WEL

#### Occupational Exposure Limits

Valid for  
Ireland

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Calcium carbonate 471-34-1 [CALCIUM CARBONATE, TOTAL INHALABLE DUST]		10	Time Weighted Average (TWA):		IR_OEL
Di-"isononyl" phthalate 28553-12-0 [DIISONONYL PHTHALATE]		5	Time Weighted Average (TWA):		IR_OEL
Titanium dioxide 13463-67-7 [TITANIUM DIOXIDE, RESPIRABLE DUST]		4	Time Weighted Average (TWA):		IR_OEL
Titanium dioxide		10	Time Weighted Average		IR_OEL

13463-67-7 [TITANIUM DIOXIDE, TOTAL INHALABLE DUST]			(TWA):		
Dibutoxydibutylstannane 3349-36-8 [TIN ORGANIC COMPOUNDS, (AS SN)]		0,2	Short Term Exposure Limit (STEL):	Indicative OELV	IR_OEL
Dibutoxydibutylstannane 3349-36-8 [TIN ORGANIC COMPOUNDS, (AS SN)]		0,1	Time Weighted Average (TWA):	Indicative OELV	IR_OEL

**Predicted No-Effect Concentration (PNEC):**

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Dibutoxydibutylstannane 3349-36-8	aqua (freshwater)		0,0019 mg/l				
Dibutoxydibutylstannane 3349-36-8	aqua (marine water)		0,00019 mg/l				
Dibutoxydibutylstannane 3349-36-8	sewage treatment plant (STP)		33 mg/l				
Dibutoxydibutylstannane 3349-36-8	sediment (freshwater)				0,193 mg/kg		
Dibutoxydibutylstannane 3349-36-8	sediment (marine water)				0,0193 mg/kg		
Dibutoxydibutylstannane 3349-36-8	soil				0,076 mg/kg		

**Derived No-Effect Level (DNEL):**

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Dibutoxydibutylstannane 3349-36-8	Workers	dermal	Acute/short term exposure - systemic effects		1 mg/kg	
Dibutoxydibutylstannane 3349-36-8	Workers	inhalation	Acute/short term exposure - systemic effects		0,07 mg/m3	
Dibutoxydibutylstannane 3349-36-8	Workers	dermal	Long term exposure - systemic effects		0,2 mg/kg	
Dibutoxydibutylstannane 3349-36-8	Workers	inhalation	Long term exposure - systemic effects		0,01 mg/m3	
Dibutoxydibutylstannane 3349-36-8	General population	dermal	Acute/short term exposure - systemic effects		0,5 mg/kg	
Dibutoxydibutylstannane 3349-36-8	General population	inhalation	Acute/short term exposure - systemic effects		0,02 mg/m3	
Dibutoxydibutylstannane 3349-36-8	General population	oral	Acute/short term exposure - systemic effects		0,01 mg/kg	
Dibutoxydibutylstannane 3349-36-8	General population	dermal	Long term exposure - systemic effects		0,08 mg/kg	
Dibutoxydibutylstannane 3349-36-8	General population	inhalation	Long term exposure - systemic effects		0,003 mg/m3	
Dibutoxydibutylstannane 3349-36-8	General population	oral	Long term exposure - systemic effects		0,002 mg/kg	

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**

Engineering controls:

Ensure good ventilation/extraction.

Respiratory protection:

In case of dust formation, we recommend wearing of appropriate respiratory protection equipment with particle filter P (EN 14387).

This recommendation should be matched to local conditions.

Hand protection:

Chemical-resistant protective gloves (EN 374). Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to > 30 minutes permeation time as per EN 374): Polychloroprene (CR;  $\geq$  1 mm thickness) or natural rubber (NR;  $\geq$  1 mm thickness) Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to > 480 minutes permeation time as per EN 374): Polychloroprene (CR;  $\geq$  1 mm thickness) or natural rubber (NR;  $\geq$  1 mm thickness) This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

Eye protection:

Protective goggles

Protective eye equipment should conform to EN166.

Skin protection:

Wear protective equipment.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

Advices to personal protection equipment:

Use only personal protection that's CE-labelled according to Directive 89/686/EEC (Europe) or to Regulation No. 819 of 19 August 1994 (Norway).

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions.

Personal protective equipment should conform to the relevant EN standard.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance	paste pasty white
Odor	characteristic
Odour threshold	No data available / Not applicable
pH	No data available / Not applicable
Melting point	No data available / Not applicable
Solidification temperature	No data available / Not applicable
Initial boiling point	No data available / Not applicable
Flash point	Not available.
Evaporation rate	No data available / Not applicable
Flammability	No data available / Not applicable
Explosive limits	No data available / Not applicable
Vapour pressure	No data available / Not applicable
Relative vapour density:	No data available / Not applicable
Density (20 °C (68 °F))	1,50 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable
Solubility	No data available / Not applicable
Solubility (qualitative) (20 °C (68 °F); Solvent: Water)	Insoluble

Partition coefficient: n-octanol/water	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Decomposition temperature	No data available / Not applicable
Viscosity (; 20 °C (68 °F); Conc.: 100 % product)	120 - 210 pa.s
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Oxidising properties	No data available / Not applicable
Solid content (105 °C )	98 %

**9.2. Other information**

No data available / Not applicable

**SECTION 10: Stability and reactivity****10.1. Reactivity**

None if used for intended purpose.

**10.2. Chemical stability**

Stable under recommended storage conditions.

**10.3. Possibility of hazardous reactions**

See section reactivity

**10.4. Conditions to avoid**

None if used for intended purpose.

**10.5. Incompatible materials**

None if used properly.

**10.6. Hazardous decomposition products**

No decomposition if used according to specifications.

**SECTION 11: Toxicological information****General toxicological information:**

An allergic reaction cannot be excluded after repeated skin contact.

**11.1. Information on toxicological effects****Acute oral toxicity:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Species	Method
Dibutoxydibutylstannane 3349-36-8	LD50	> 2.000 mg/kg	rat	OECD Guideline 420 (Acute Oral Toxicity)
Dibutoxydibutylstannane 3349-36-8	Acute toxicity estimate (ATE)	2.500 mg/kg		Expert judgement

**Acute dermal toxicity:**

No data available.

**Acute inhalative toxicity:**

No data available.

**Skin corrosion/irritation:**

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Exposure time	Species	Method
Dibutoxydibutylstannane 3349-36-8	corrosive	24 h	rat	Expert judgement

**Serious eye damage/irritation:**

No data available.

**Respiratory or skin sensitization:**

No data available.

**Germ cell mutagenicity:**

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Dibutoxydibutylstannane 3349-36-8	positive	in vitro mammalian chromosome aberration test	with and without		OECD Guideline 473 (In vitro Mammalian Chromosome Aberration Test)

**Carcinogenicity**

No data available.

**Reproductive toxicity:**

The mixture is classified based on threshold limits referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Result / Value	Test type	Route of application	Species	Method
Dibutoxydibutylstannane 3349-36-8	NOAEL P 1,9 - 2,3 mg/kg	screening	oral: feed	rat	OECD Guideline 421 (Reproduction / Developmental Toxicity Screening Test)

**STOT-single exposure:**

No data available.

**STOT-repeated exposure::**

No data available.

**Aspiration hazard:**

No data available.



## SECTION 12: Ecological information

### General ecological information:

Do not empty into drains, soil or bodies of water.

### 12.1. Toxicity

#### Toxicity (Fish):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Dibutoxydibutylstannane 3349-36-8	LC50	> 3,1 mg/l		Brachydanio rerio (new name: Danio rerio)	OECD Guideline 203 (Fish, Acute Toxicity Test)

#### Toxicity (Daphnia):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Dibutoxydibutylstannane 3349-36-8	EC50	1,9 mg/l	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)

#### Chronic toxicity to aquatic invertebrates

No data available.

#### Toxicity (Algae):

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Dibutoxydibutylstannane 3349-36-8	EC50	> 2 mg/l	72 h	Scenedesmus subspicatus (new name: Desmodesmus subspicatus)	OECD Guideline 201 (Alga, Growth Inhibition Test)

#### Toxicity to microorganisms

The mixture is classified based on calculation method referring to the classified substances present in the mixture.

Hazardous substances CAS-No.	Value type	Value	Exposure time	Species	Method
Dibutoxydibutylstannane 3349-36-8	EC50	> 1.000 mg/l	3 h	activated sludge of a predominantly domestic sewage	OECD Guideline 209 (Activated Sludge, Respiration Inhibition Test)

### 12.2. Persistence and degradability

No data available.

### 12.3. Bioaccumulative potential

No data available.

### 12.4. Mobility in soil

No data available.

#### 12.5. Results of PBT and vPvB assessment

Hazardous substances CAS-No.	PBT / vPvB
Dibutoxydibutylstannane 3349-36-8	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

#### 12.6. Other adverse effects

No data available.

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

Product disposal:

In consultation with the responsible local authority, must be subjected to special treatment.

Waste code

08 04 10 Waste adhesives and sealants other than those mentioned in 08 04 09.

Waste code

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

### SECTION 14: Transport information

#### 14.1. UN number

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.4. Packing group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.7. Transport in bulk according to Annex II of Marpol and the IBC Code

not applicable

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content 0 %  
(VOCV 814.018 VOC regulation  
CH)

VOC content 0 %  
(2010/75/EU)

**VOC Paints and Varnishes (EU):**

Product (sub)category:

This product is not a subject of the Directive 2004/42/EC

**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

**SECTION 16: Other information**

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H314 Causes severe skin burns and eye damage.

H317 May cause an allergic skin reaction.

H341 Suspected of causing genetic defects.

H360FD May damage fertility. May damage the unborn child.

H370 Causes damage to organs.

H372 Causes damage to organs through prolonged or repeated exposure.

H411 Toxic to aquatic life with long lasting effects.

**Further information:**

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**