


DO NOT SCALE DRAWING

REVISION

A INITIAL DRAWING 21.9.15



Part Number	ØA	B Nom	C Max	D Nom	E Min	F Length
M3 10 PSBRMC N100	M3-0.5	6.0	1.8	0.8	0.7	10
M3 12 PSBRMC N100	M3-0.5	6.0	1.8	0.8	0.7	12
M4 6 PSBRMC N100	M4-0.7	8.0	2.4	1.2	1.0	6
M4 12 PSBRMC N100	M4-0.7	8.0	2.4	1.2	1.0	12
M4 16 PSBRMC N100	M4-0.7	8.0	2.4	1.2	1.0	16
M4 20 PSBRMC N100	M4-0.7	8.0	2.4	1.2	1.0	20
M4 25 PSBRMC N100	M4-0.7	8.0	2.4	1.2	1.0	25
M4 30 PSBRMC N100	M4-0.7	8.0	2.4	1.2	1.0	30
M5 12 PSBRMC N100	M5-0.8	10.0	3.0	1.2	1.2	12
M5 20 PSBRMC N100	M5-0.8	10.0	3.0	1.2	1.2	20

NOTES:



UNLESS OTHERWISE SPECIFIED:
DIMENSIONS ARE IN MM (MILLIMETERS).
SURFACE FINISH:
TOLERANCES: DIN 85

MATERIAL:
Brass

TITLE:
Slotted Pan Head Machine Screw DIN 85

	NAME	DATE
DRAWN	Darryl Wilson	21.09.15
CHK'D		
APPVD		

HEAT TREATMENT:
N/A

DESIGN RIGHT. TR FASTENINGS LTD, 2003
UNDER NO CIRCUMSTANCES MUST THIS
DRAWING BE COPIED OR DISCLOSED
WITHOUT FIRST OBTAINING WRITTEN
AUTHORITY.

CUSTOMER PART NUMBER:
N/A

FINISH:
BN2 - Commercial Nickel Plated

DRAWING NUMBER:
TR32PSBRMC

A4