

# TECHNICAL DATA SHEET

**PRO-ELEC**

## Polyester Textile Sleeve CB19661-CB19664

**RoHS  
Compliant**

| Specification   |  |
|-----------------|--|
| Material        | Polyester                                |
| Operating range | -50°C~150°C                              |
| Melting point   | 240±10°C                                 |
| Standard colour | Black (white printing) others on request |
| Certification   | RoHS, ISO6945, MSHA                      |
| Cutting tool    | Scissors and hot knife                   |


### Conditions of use

1. Polyester textile sleeve consists of polyester multifilament. With the particularly smooth inner wall, it could reduce the frictional resistance problems, provides easy installation. The tight woven construction helps dispense the flow of fluid in a rupture hose.
2. It is widely used to protect hydraulic pipes, rubber hose, plastic pipes, wire harnesses from damage. This kind of sleeving can also be used in industrial and construction fields where outstanding hose protection is required.

| Flat Width | Round I.D | Wall Thickness | Packing   |
|------------|-----------|----------------|-----------|
| 27         | 17        | 1.0            | 50m Spool |
| 31         | 20        | 1.0            | 50m Spool |
| 36         | 23        | 1.0            | 50m Spool |
| 39         | 25        | 1.0            | 50m Spool |
| 42         | 27        | 1.0            | 50m Spool |
| 49         | 31        | 1.0            | 50m Spool |
| 52         | 33        | 1.0            | 50m Spool |
| 54         | 36        | 1.0            | 50m Spool |
| 63         | 40        | 1.0            | 50m Spool |

| Flat Width | Round I.D | Wall Thickness | Packing   |
|------------|-----------|----------------|-----------|
| 69         | 44        | 1.0            | 50m Spool |
| 74         | 47        | 1.0            | 50m Spool |
| 83         | 53        | 1.0            | 50m Spool |
| 86         | 55        | 1.0            | 50m Spool |
| 94         | 60        | 1.0            | 50m Spool |
| 104        | 66        | 1.0            | 50m Spool |
| 115        | 73        | 1.0            | 50m Spool |
| 146        | 93        | 1.0            | 50m Spool |
| 176        | 112       | 1.0            | 50m Spool |

| Description                                | Code         |
|--|--------------|
| Polyester Protective Sleeve ID25 Black 50m | BPPS25BLK50M |
| Polyester Protective Sleeve ID40 Black 50m | BPPS40BLK50M |
| Polyester Protective Sleeve ID25 Black 25m | BPPS25BLK25M |
| Polyester Protective Sleeve ID40 Black 25m | BPPS40BLK25M |



**Important Notice :** This data sheet and its contents (the "Information") belong to pro-ELEC. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-ELEC assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-ELEC was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-ELEC's liability for death or personal injury resulting from its negligence.

**PRO-ELEC**