

90 22 02 SB

KNIPEX TwistCut Corrugated Pipe Cutter



- For corrugated pipes with Ø of 13 - 32 mm
- For cutting empty or ready-assembled corrugated pipes to length
- Application in the electrical and construction trades and for plumbing work
- Recessed blades prevent injuries
- Exact, flush cut, without damaging the internal cables
- Cut on the outside of fluting - no sharp raw edge inside the corrugated pipe
- Fast and reliable work
- Simple insertion of the corrugated pipe for reliable and simple cutting: no waste
- In the case of thick-walled corrugated pipes, reapply after the circular cut just behind the cut, and break off the corrugated pipe
- Slim and ergonomically shaped for work in poorly accessible areas
- Double-sided guide for a precise cut
- Body made of stable polyamide compound plastic



Internal cables cannot be damaged when cutting the corrugated pipes externally on the ridge. As a result, the inner pipe end at the cut point always indicates a radius, so that no line is damaged during subsequent movements of the conductors or when inserting a new or additional conductor.

Article No.	90 22 02 SB
EAN	4003773082293
Cutting capacities (diameter) Ø mm	13 - 32
Wire stripping value for conductors and strands mm²	0,2 - 4,0
Length mm	100
Net weight g	46



Clean cutting edge with no damage to internal cables as the cut is always at the top of the corrugation



90 22 02 SB: Practical locator simplifies the insertion of single conductors for stripping



90 22 02 SB: Injection moulded length scale for consistent stripping to a uniform length, legible for left and right handed users

technical change and errors excepted